

TECHNICAL DATA SHEET

Part No. TSR2W-14
Article No. 250-02142
Type TSR2-14



HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSR surface raceway systems can be used to route a variety of communication cable, including high speed UTP and fiber optic cable.

Description	Splice Cover, 1-1/4"
Height (imperial)	0.825 "
Height (metric)	20.96 mm
Length (imperial)	2.000 "
Length (metric)	50.80 mm
Width (imperial)	1.479 "
Width (metric)	37.57 mm

RoHS ✓

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	10
Carton Qty.	500
Customs Number	3925900000