

TECHNICAL DATA SHEET

Part No. 321-30100
Article No. 321-30100
Type HA67-33.0/5.5



HA47 is a thick-wall adhesive lined heat shrink tubing for use in applications up to 1000 volts. The adhesive lining provides excellent moisture sealing and weather protection, making it suitable for above and below ground applications. Made of a polyolefin outer material, this tubing has a shrink ratio up to 3.5 to 1. The adhesive lining begins to activate as the temperature approaches 185° F (85° C).

Material	Polyolefin, cross-linked (PO-X)
Adhesive	Hot melt adhesive
Shrink Ratio	6:1
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature	+248 °F (+120 °C)
Operating Temperature	-67°F to +230°F (-55°C to +110°C)
Dielectric Strength	20 kV/mm
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	3
Carton Qty.	108
Customs Number	3926909988

Adhesive	Hot melt adhesive
Dielectric Strength	20 kV/mm
Length (imperial)	4 ft
Length (metric)	1.2 m
Recovered Diameter (metric)	5.5 mm
Shrink Ratio	6:1
Supplied Diameter (metric)	33.0 mm
Tensile Strength	14 MPa
Wall Thickness (metric)	3.4 mm

