

TECHNICAL DATA SHEET

Part No. 553-60046
Article No. 553-60046
Type TLFX95DS-3x16WH



ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.

Center Slit	2-Slit
Height (imperial)	0.62 "
Height (metric)	16.0 mm
Width (imperial)	0.63 "
Width (metric)	16.0 mm

HF✓

LFH✓

RoHS✓

EN 45545-2

ASTM

NFPA 130

Material	Polyolefin, cross-linked (PO-X)
Shrink Ratio	2:1
Longitudinal Change After Shrinkage	-5% max.
Min. Shrink Temperature	+212 °F (+100 °C)
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Dielectric Strength	20 kV/mm
Abrasion Resistance	High
Flammability	UL 224
Halogen Free	Yes
UV Resistant	No
US MILSPEC	MIL-STD-202J, SAE AS5942 3.4.1
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	7500
Carton Qty.	1
Customs Number	3917320000