


## Common Mode Choke

TCK-177


<b>Order Code</b>	TCK-177
<b>Inductance (each winding)</b>	398 $\mu$ H $\pm 35\%$ (at 100 kHz / 100 mV)
<b>Impedance (DCR)</b>	8.5 m $\Omega$ max.
<b>Rated Current</b>	10.05 A max.
<b>Rated Voltage</b>	500 VDC max. (between windings)
<b>Operating Temperature</b>	-40°C to +105°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-177">www.tracopower.com/overview/tck-177</a>




## Impedance Curve



## Outline Dimensions



Dimensions [mm]	
A	16.0 max.
B	16.0 max.
C	15.0 max.
D	4.0 $\pm 0.3$
E	10.0 $\pm 0.3$
F	7.4 $\pm 0.3$
G	$\varnothing 0.8 \pm 0.1$



All specifications valid at +25°C, unless otherwise stated.