




<b>Order Code</b>	<b>TCK-183</b>
<b>Inductance</b> (each winding)	545 $\mu\text{H} \pm 35\%$ (at 100 kHz / 100 mV)
<b>Impedance</b> (DCR)	8.6 m $\Omega$ max.
<b>Rated Current</b>	13 A max.
<b>Operating Temperature</b>	40°C to +125°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-183">www.tracopower.com/overview/tck-183</a>



### Impedance Curve



### Outline Dimensions



Dimensions [mm]	
<b>A</b>	14.45 max.
<b>B</b>	5.0 $\pm 2$
<b>C</b>	10.0 $\pm 1$
<b>D</b>	4.0 $\pm 1$
<b>E</b>	$\varnothing 1.0 \pm 1$

All specifications valid at +25°C, unless otherwise stated.