



<b>Order Code</b>	TCK-191
<b>Inductance</b>	1 $\mu$ H $\pm 20\%$ (at 100 kHz / 1 V)
<b>Impedance (DCR)</b>	3.3 m $\Omega$ max.
<b>Rated Current</b>	19 A max.
<b>Operating Temperature</b>	-40°C to +125°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-191">www.tracopower.com/overview/tck-191</a>



### Impedance Curve



### Outline Dimensions



Dimensions [mm]	
A	10.0 $\pm 0.5$
B	10.0 $\pm 0.5$
C	4.2 max.
D	11.7 max.
E	2.0 $\pm 0.7$
F	3.0 $\pm 0.7$
G	5.4
H	13.6
I	4.1

All specifications valid at +25°C, unless otherwise stated.