


- **Highly cost efficient design**
- **I/O isolation: 4'000 VDC**
- **Operating temperature range -40 to +85 °C without derating**
- **5 VDC (±10%) input voltage range**
- **Unregulated outputs**
- **Efficiency up to 79%**
- **Industry standard SIP-7 package**
- **3-year product warranty**



The TEA 1HI is an unregulated 1 Watt DC/DC SIP-7 converter series with high isolation which is specifically designed to offer a low-cost solution while keeping a high quality standard. This new series focuses on a simple but effective design approach, which minimizes component and labor cost and is complemented with a complete automatization of the manufacturing process. An operating temperature range from -40°C to 85°C without derating and an I/O-isolation of 4'000 VDC enables this series to cover many different applications. The industry standard package of this converter offers a broad application range in any space, cost critical application and is especially suited for high volume projects where simple but reliable products are needed.

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TEA 1-0505HI	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	200 mA	79 %

### Input Specifications

Surge Voltage	9 VDC max. (1 s max.)
Recommended Input Fuse	800 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter	Internal Capacitor

### Output Specifications

Voltage Set Accuracy	±3% max. (at 60 % load)
Regulation (Unregulated)	- Input Variation (1% Vin step) - Load Variation See application note: <a href="http://www.tracopower.com/tea1hi-cc">www.tracopower.com/tea1hi-cc</a>
Ripple and Noise	- 20 MHz Bandwidth 100 mVp-p max. 50 mVp-p typ.
Capacitive Load	2'200 µF max.
Minimum Load	See application note: <a href="http://www.tracopower.com/tea1hi-cc">www.tracopower.com/tea1hi-cc</a>
Temperature Coefficient	±0.02 %/K max.
Start-up Time	10 ms max.
Short Circuit Protection	Limited 1 s max., Automatic recovery

### Safety Specifications

Standards	- IT / Multimedia Equipment	Designed for IEC/EN/UL 62368-1 (not certified)
Over Voltage Category		Not mains connected

### General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +95°C +105°C max. -55°C to +125°C
Power Derating	- High Temperature See application note: <a href="http://www.tracopower.com/tea1hi-cc">www.tracopower.com/tea1hi-cc</a>	5.0 %/K above 85°C
Cooling System		Natural convection (20 LFM)
Switching Frequency		150 kHz max. (Royer) 80 kHz typ. (Royer)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	4'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	10 pF typ.
Reliability	- Calculated MTBF	2'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Housing Material		Plastic (UL 94 V-0 rated)
Potting Material		Epoxy (UL 94 V-0 rated)
Pin Material		Phosphor Bronze (C5191)
Pin Foundation Plating		Nickel (1 µm min.)
Pin Surface Plating		Tin (3 µm min.), bright
Housing Type		Plastic Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		SIP7
Soldering Profile		Lead-Free Wave Soldering 265 °C / 5 s max.
Weight		2.3 g

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

[www.tracopower.com/info/reach-declaration.pdf](http://www.tracopower.com/info/reach-declaration.pdf)

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

[www.tracopower.com/info/rohs-declaration.pdf](http://www.tracopower.com/info/rohs-declaration.pdf)

Exemptions: 7(a), 7(c)-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))

- SCIP Reference Number

c75f4061-29c7-4520-81da-a857cb7778d0

### Additional Information

Supporting Documents

[www.tracopower.com/overview/tea1hi](http://www.tracopower.com/overview/tea1hi)


Frequently Asked Questions

[www.tracopower.com/glossary-faq](http://www.tracopower.com/glossary-faq)

Glossary

[www.tracopower.com/info/glossary.pdf](http://www.tracopower.com/info/glossary.pdf)

### Outline Dimensions



Pinout	
Pin	Function
1	+Vin (Vcc)
2	-Vin (GND)
5	-Vout
7	+Vout

Dimensions in mm (inch)

Tolerances: x.x ±0.5 (x.xx ±0.02)

x.xx ±0.25 (x.xxx ±0.01)

Pin dimension tolerance: ±0.1 (±0.004)

