TRACO POWER

DC/DC Converter

TMR 9WI Series, 9 Watt

- **Highest power density in SIP-8 metal package (optional plastic package)**
- **Ultra wide 4:1 input voltage range**
- **Temperature range –40° to +85°C**
- **High efficiency up to 89%**
- **Indefinite short-circuit protection**
- **I/O isolation 1'600 VDC**
- **Remote On/Off control**
- **Fully RoHS compliant**
- **3-year product warranty**



UL 62368-1 IEC 62368-1

The TMR 9WI series is a new family of isolated 9W DC/DC converter modules with regulated output, featuring ultra wide 4:1 input voltage ranges. The product comes in a ultra-compact SIP-8 metal package with a small footprint occupying only 2.0 cm² (0.3 square inch) of board space.
An excellent efficiency allows –40° to +60°C operation temperatures without derating. Further features include remote On/Off control and continuous short circuit protection. The very compact dimensions of these converters make them an ideal solution for many space critical applications in communication equipment, instrumentation and industrial electronics.

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency
		Vnom	Imax	Vnom	Imax	typ.
TMR 9-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2'000 mA			82 %
TMR 9-2411WI		5 VDC	1'600 mA			85 %
TMR 9-2419WI		9 VDC	1'000 mA			88 %
TMR 9-2412WI		12 VDC	750 mA			88 %
TMR 9-2413WI		15 VDC	600 mA			89 %
TMR 9-2415WI		24 VDC	375 mA			89 %
TMR 9-2421WI		+5 VDC	800 mA	–5 VDC	800 mA	86 %
TMR 9-2422WI		+12 VDC	375 mA	–12 VDC	375 mA	88 %
TMR 9-2423WI		+15 VDC	300 mA	–15 VDC	300 mA	88 %
TMR 9-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2'000 mA			82 %
TMR 9-4811WI		5 VDC	1'600 mA			85 %
TMR 9-4819WI		9 VDC	1'000 mA			89 %
TMR 9-4812WI		12 VDC	750 mA			89 %
TMR 9-4813WI		15 VDC	600 mA			89 %
TMR 9-4815WI		24 VDC	375 mA			89 %
TMR 9-4821WI		+5 VDC	800 mA	–5 VDC	800 mA	85 %
TMR 9-4822WI		+12 VDC	375 mA	–12 VDC	375 mA	88 %
TMR 9-4823WI		+15 VDC	300 mA	–15 VDC	300 mA	87 %

Options

on demand (backorder with MOQ non stocking item)	- Optional models with plastic case

Input Specifications

Input Current	- At no load	24 Vin models:	**7 mA typ.**
		48 Vin models:	**3 mA typ.**
	- At full load	24 Vin models:	**350 mA max.** (3.3 Vout model)
			407 mA max. (5 Vout model)
			434 mA max. (9 Vout model)
			439 mA max. (12 Vout model)
			440 mA max. (15 Vout model)
			431 mA max. (24 Vout model)
			399 mA max. (5 / -5 Vout model)
			434 mA max. (12 / -12 Vout model)
			434 mA max. (15 / -15 Vout model)
		48 Vin models:	**173 mA max.** (3.3 Vout model)
			203 mA max. (5 Vout model)
			217 mA max. (9 Vout model)
			219 mA max. (12 Vout model)
			218 mA max. (15 Vout model)
			215 mA max. (24 Vout model)
			201 mA max. (5 / -5 Vout model)
			218 mA max. (12 / -12 Vout model)
			222 mA max. (15 / -15 Vout model)
Surge Voltage		24 Vin models:	**50 VDC max.** (1 s max.)
		48 Vin models:	**100 VDC max.** (1 s max.)
Recommended Input Fuse		24 Vin models:	**3'150 mA** (slow blow)
		48 Vin models:	**1'250 mA** (slow blow)
			(The need of an external fuse has to be assessed in the final application.)
Input Filter			Internal Capacitor

Output Specifications

Voltage Set Accuracy			±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models:	0.2% max.
		dual output models:	0.2% max.
	- Load Variation (0 - 100%)	single output models:	1% max.
		dual output models:	**1% max.** (Output 1)
			1% max. (Output 2)
	- Cross Regulation (25% / 100% asym. load)	dual output models:	5% max.
Ripple and Noise (20 MHz Bandwidth)	- single output	3.3 Vout models:	**50 mVp-p typ.** (w/ 1 µF X7R)
		5 Vout models:	**50 mVp-p typ.** (w/ 1 µF X7R)
		9 Vout models:	**50 mVp-p typ.** (w/ 1 µF X7R)
		12 Vout models:	**75 mVp-p typ.** (w/ 1 µF X7R)
		15 Vout models:	**75 mVp-p typ.** (w/ 1 µF X7R)
		24 Vout models:	**75 mVp-p typ.** (w/ 1 µF X7R)
	- dual output	5 / -5 Vout models:	**50 / 50 mVp-p typ.** (w/ 1 µF X7R)
		12 / -12 Vout models:	**75 / 75 mVp-p typ.** (w/ 1 µF X7R)
		15 / -15 Vout models:	**75 / 75 mVp-p typ.** (w/ 1 µF X7R)
Capacitive Load	- single output	3.3 Vout models:	**2'600 µF max.**
		5 Vout models:	**1'300 µF max.**
		9 Vout models:	**800 µF max.**
		12 Vout models:	**560 µF max.**
		15 Vout models:	**560 µF max.**
		24 Vout models:	**200 µF max.**
	- dual output	5 / -5 Vout models:	**800 / 800 µF max.**
		12 / -12 Vout models:	**390 / 390 µF max.**
		15 / -15 Vout models:	**200 / 200 µF max.**
Minimum Load			Not required

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Temperature Coefficient		±0.02 %/K max.
Start-up Time		50 ms typ.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		180% typ. of Iout max.
Transient Response	- Response Time	250 µs typ. (25% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Certification Documents	www.tracopower.com/tmr9wi-safety-cert/
Energy Source	- Output, acc. to 62368-1	ES2
Power Source	- Output, acc. to 62368-1	PS3
Pollution Degree		PD 2
Over Voltage Category		Not mains connected

EMC Specifications

EMI (Emissions)	- Conducted Emissions		EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions		EN 55032 class A (with external filter) EN 55032 class B (with external filter)
		External filter proposal:	www.tracopower.com/tmr9wi-emc-filter/
EMS (Immunity)	- Electrostatic Discharge	Air:	EN 61000-4-2, ±8 kV, perf. criteria A
		Contact:	EN 61000-4-2, ±6 kV, perf. criteria A
	- RF Electromagnetic Field		EN 61000-4-3, 20 V/m, perf. criteria A
	- EFT (Burst) / Surge		EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±2 kV, perf. criteria A
		Ext. input component:	24 Vin models: KY 220 µF || SMDJ70A 48 Vin models: KY 220 µF || SMDJ120A
	- Conducted RF Disturbances		EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous:	EN 61000-4-8, 100 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	–40°C to +85°C
	- Case Temperature	+100°C max.
	- Storage Temperature	–55°C to +125°C
Power Derating	- High Temperature	Depending on model
	See application note:	www.tracopower.com/tmr9wi-cc/
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote (passive = on)	On: 0 to 0.5 VDC or open circuit Off: 3 to 12 VDC Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current	2.5 mA max.
Altitude During Operation		5'000 m max.
Regulator Topology		Flyback Converter
Switching Frequency		400 kHz typ. (PWM) (single output models) 500 kHz typ. (PWM) (dual output models)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'600 VDC
	- Input to Case, 60 s	1'000 VDC
	- Output to Case, 60 s	1'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Isolation Capacitance	- Input to Output, 100 kHz, 1 V	50 pF max.
Reliability	- Calculated MTBF	2'940'000 h (for standard version) 2'640'000 h (for plastic version) (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Environment	- Vibration	MIL-STD-810F
	- Thermal Shock	MIL-STD-810F
Housing Material		Copper (for standard version) non-conductive plastic (for plastic version)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper
Pin Foundation Plating		Nickel (2 - 3 µm)
Pin Surface Plating		Tin (3 - 5 µm), matte
Housing Type		Metal Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		SIP8
Soldering Profile		Lead-Free Wave Soldering 260°C / 6 s max.
Weight		5.9 g (for standard version) 4.8 g (for plastic version)
Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7(a), 7(c)-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)
	- SCIP Reference Number	d8371d3a-5c43-4990-a9e2-1a156c2ee4ba


Additional Information

Supporting Documents	www.tracopower.com/overview/tmr9wi
Frequently Asked Questions	www.tracopower.com/glossary-faq
Glossary	www.tracopower.com/info/glossary.pdf
Service Portal	www.tracoserviceportal.com


All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions

Metal package (standard)



Dimensions in mm (inch)
Tolerances: x.x ±0.5 (x.xx ±0.02)
x.xx ±0.25 (x.xxx ±0.01)
Pin dimension tolerance: ±0.1 (±0.004)




Pinout		
Pin	**Single Output**	**Dual Output**
1	–Vin (GND)	–Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	–Vout	Common
8	NC	–Vout
9	Case	Case
10	Stand Off	Stand Off
11	Stand Off	Stand Off
12	Case	Case

Avoid routing PCB traces under the converter.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Plastic package (option)



Dimensions in mm (inch)
Tolerances: x.x ±0.5 (x.xx ±0.02)
x.xx ±0.25 (x.xxx ±0.01)
Pin dimension tolerance: ±0.1 (±0.004)

Pinout		
Pin	**Single Output**	**Dual Output**
1	–Vin (GND)	–Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	–Vout	Common
8	NC	–Vout

Avoid routing PCB traces under the converter.

© Copyright 2026 Traco Electronic AG