




All dimensions are in mm

Documents

Interface	RN_121-01
Panel piercing	MB_633
Pinning	RN_143-01
Tape & reel packaging	VG375.21000

Material and plating

Connector parts

Signal contact

Outer contact

Dielectric

Housing

Material

Brass

Zinc alloy

LCP

HTN (c00)

Plating / Colour

Gold, min. 0.12 µm, over Nickel (Interface)

Tin, min. 3 µm, over Nickel (PCB)

Tin, min. 3 µm, over Nickel

nature

see section "Coding"

Electrical data

Impedance	100 Ω
Frequency	DC to 10 GHz
Return loss	≥ 30 dB, 0.01 GHz to 3 GHz
	≥ 25 dB, 3 GHz to 6 GHz
	≥ 20 dB, 6 GHz to 10 GHz
Insulation resistance	≥ 100 M Ω
Signal contact resistance	≤ 10 m Ω
Outer contact resistance	≤ 7.5 m Ω
Working voltage	≤ 60 V DC
Power current	≤ 1.5 A DC

Connector only, electrical data in application depends decisively on PCB layout

Mechanical data

Mating cycles	min. 25
Engagement force	≤ 20 N
Retention force latch	≥ 110 N
Coding efficiency	≥ 150 N
Weight	4.4 g

Environmental data

Temperature range	-40 °C to +105 °C
Thermal shock	DIN EN 60068-2-14
Humidity	DIN EN 60068-2-30 @ +40 °C
Dry heat	DIN EN 60068-2-2 @ +105 °C
Vibration	DIN EN 60068-2-64
Mechanical shock	DIN EN 60068-2-27
Soldering profile	DIN EN 60068-2-58; Group 3 (250 °C / 30 sec.)
RoHS	compliant

Packing

Standard	210 pcs in tape & reel
----------	------------------------

Technical Data Sheet

Rosenberger

H-MTD®

RIGHT ANGLE PLUG
FOR PCB

E6S20A-40MT5-Y

Coding

Part number has to be accomplished by codification

Coding	Plug	Colour	RAL	Part-Number
A		jet black	sim. 9005	E6S20A-40MT5-A
B		pure white	sim. 9010	E6S20A-40MT5-B
C		light blue	sim. 5012	E6S20A-40MT5-C
D		claret violet	sim. 4004	E6S20A-40MT5-D
E		may green	sim. 6017	E6S20A-40MT5-E
F		nut brown	sim. 8011	E6S20A-40MT5-F
G*		platinum grey	sim. 7036	E6S20A-40MT5-G
H*		light pink	sim. 3015	E6S20A-40MT5-H
J*		beige	sim. 1001	E6S20A-40MT5-J
K*		curry	sim. 1027	E6S20A-40MT5-K
L*		yellow green	sim. 6018	E6S20A-40MT5-L
M*		pastel orange	sim. 2003	E6S20A-40MT5-M
O*		light green	sim. 6027	E6S20A-40MT5-O
Z		water blue	sim. 5021	E6S20A-40MT5-Z

* Coding on request

Change history

Revision	Description	Position
c00	Raw material supplier change due to dual source strategy	Sheet 1

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
J. Schmid	19.03.18	F. Weinbender	21.01.26	c00	25-1622	C. Hennersperger	21.01.26
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 3 / 3