

THIS IS ISSUED IN STRICT CONFIDENCE
THAT IT IS NOT USED AS A BASIS FOR
MANUFACTURE OR SALE AND THAT IT IS
NOT COPIED, REPRINTED OR
DISCLOSED TO A THIRD PARTY EITHER
WHOLLY OR IN PART WITHOUT THE
PRIOR WRITTEN CONSENT OF CAL TEST
ELECTRONICS, INC.


REVISONS

REV.	DESCRIPTION	DATE	APPROVED
A	CLASS A RELEASE (REFERENCE DWG P288200).	8/6/2025	B. Hansen

D NOTES:

1. MATERIAL:
 - INNER JACKET: PVC, WHITE.
 - OUTER JACKET: PVC, SEE MODEL NUMBER TABLE.
 - CONDUCTOR: 7x72(504)/0.08±0.08 mm, (2.50 mm²), BARE COPPER, 13 AWG.
 - O.D.: Ø 3.90±0.05 mm (0.154±0.002).
2. RATING:
 - VOLTAGE: 1000 V CAT IV (IEC 61010-031).
 - CURRENT: 36 A MAX.
 - TEMPERATURE: -20°C TO +80°C.
3. AVAILABLE IN 3 STANDARD LENGTHS AND IN 6 DIFFERENT COLORS - REFER TO MODEL NUMBER TABLE
4. RoHS 2 COMPLIANT.

C 5. MARKING: CT PVC DJ 2.50mm² □ Cal Test Electronics.




MODEL NUMBER
CT2882A-#-L

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

THIRD ANGLE PROJECTION



UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN MILLIMETERS
TOLERANCES ARE:

XX = ±0.5 XX* = ±0.5*
XXX = ±0.25
XXXX = ±0.125
DO NOT SCALE DRAWING

MATERIAL
SEE NOTES

PROJECT NO.

A801

APPROVALS

DATE

DRAWN

WDH

CHECKER

ENGR.

B. Hansen

DESIGN ACTIVITY

FINISH

NONE

SCALE

2:1

METRIC

Cal Test
ELECTRONICS

22820 Savi Ranch Prky.
Yorba Linda, CA 92887
USA

WIRE, TEST LEAD, PVC JACKET,
2.50mm², 13 AWG, 36 A

CT2882A

REV.
A

SHEET 1 OF 1