



WSMP

Female to 2.92mm Female
Test Adapter

W1K102-K00D3



All dimensions are in inches [mm]

Unless otherwise specified, tolerances are as follows: .XXX ± .001 [0,025] .XXXX ± .0005 [0,012]

Interface

According to

Rosenberger WSMP™ Interface standards

Material and plating**Connector parts**

WSMP (F) Body and Contact

Material

CuBe per ASTM B196

PlatingHard gold 50µIN [1,27µm] min over
Nickel 50µIN [1,27µm] min

2.92mm Body

Stainless Steel per
ASTM A582

Passivated

Dielectric

PTFE PER ASTM D1710

Dielectric

Ultem® 1000 PER D5205

Technical Data Sheet

Rosenberger

WSMP

Female to 2.92mm Female
Test Adapter

W1K102-K00D3

Electrical data

Impedance	50 Ω
Frequency	DC to 40 GHz
Return loss (typical)	≥ 19 dB, DC to 40 GHz
Insertion loss	≤ 0.12 x $\sqrt{f(\text{GHz})}$ dB
Insulation resistance	≥ 3,500 MΩ
Center contact resistance	≤ 6.0 mΩ
Outer contact resistance	≤ 2.0 mΩ
Test voltage (at sea level)	250 V rms
RF High Potential (at sea level)	150 V rms @ 5 MHz
RF leakage	≥ -80 dB @ 3 GHz (typical mated pair)

Mechanical data

Mating cycles	
- Full Detent	≥ 100
- Smooth Bore	≥ 500
- Ultra Smooth Bore	≥ 500
Engagement force (typical)	
- Full Detent	2.5 lb _f [11 N]
- Smooth Bore	1.2 lb _f [5.3 N]
- Ultra Smooth Bore	1.0 lb _f [4.5 N]
Disengagement force (typical)	
- Full Detent	4.5 lb _f [20 N]
- Smooth Bore	1.0 lb _f [4.5 N]
- Ultra Smooth Bore	1.0 lb _f [4.5 N]

Environmental data

Temperature range	-55°C to +165°C
Thermal shock	MIL-STD-202-107, Condition B
Corrosion	MIL-STD-202-101
Vibration	MIL-STD-202-204, Condition D
Shock	MIL-STD-202-213, Condition I
Moisture resistance	MIL-STD-202-106, except Step 7B
2002/95/EC (RoHS)	compliant

Tooling

Extraction tool	N/A
-----------------	-----

Suitable cables

N/A

Packing

Standard

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
R. Hosler	8/18/14	M. Peeran	8/18/14	a00	Released per 19-s000	P. Sill	1/11/19
Rosenberger of North America, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com				Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com			
				Page 2 / 2			