





Housing Material: Polyester, Black UL94V-0
Contacts: Phosphor Bronze 30µin Au plating over Ni
Leads: Matte Sn over Ni
Shield: Cu Alloy with Ni plating 40µin min
Durability: 1000 mating cycles
Dimensions: Inch [mm]
Tolerances: ±0.008 inch if not specified



RECOMMENDED P.C. BOARD PATTERN (COMP. SIDE)



PART NO. : HFJ11-E1G16E-L55RL

FASTJACK™ WITH 1000BASE-T MAGNETICS


RoHS COMPLAINT

COMPATIBLE TO LEAD-FREE WAVE SOLDERING PROCESS
FOR THROUGH HOLE COMPONENTS

EXTENDED OPERATING TEMPERATURE -40/+85°C

ELECTRICAL SPECIFICATIONS @ 25°C

URNS RATIO	1:1 ±3%
OCL (100KHz,0.1V,8mA)	350µH min
INSERTION LOSS	
1-100MHz	-1.1dB max
RETURN LOSS	
1-40MHz	-18dB min
60MHz	-14dB min
80MHz	-12dB min
100MHz	-10dB min
CROSSTALK 1-100MHz	-35dB typ
CMR 1-30MHz	-38dB typ
30-60MHz	-35dB typ
60-100MHz	-30dB typ
ISOLATION	1,500Vrms



HALO/PBL

CALIFORNIA, USA
KOWLOON, HONG KONG
SINGAPORE

TITLE FastJack™ SINGLE

FOR GIGABIT ETHERNET

PART NO. HFJ11-E1G16E-L55RL

SCALE NONE

PAGE 1 OF 1

SIGNATURES

DRAWN LI ZHI ZHONG

CHECKED LEI KEONG

APPROVED PETER LU

FILE E1G16E-L55RL.DWG

DATE

2/3/15

2/3/15

2/3/15

REV.

A

DESC.

FIRST ISSUE

DATE

2/3/15

