





DIMENSIONS: Inch [mm]
CO-PLANARITY: 0.004 [0.10]
TOLERANCES: ±0.005 INCH IF NOT SPECIFIED



PART NO. : TG91-S024NXRL

FOUR PORT T1/E1 ISOLATION TRANSFORMER MODULE
COMPATIBLE TO USE WITH TELELINK (TECCOR) DEVICES

RoHS COMPLIANT

COMPATIBLE TO LEAD-FREE SOLDERING PROCESS
CONDITION PER IPC/JEDEC J-STD-020C

UL/EN60950 AND DEMKO RECOGNIZED

OPERATING TEMPERATURE -40/+85°C

ELECTRICAL SPECIFICATIONS @25° C

URNS RATIO

TX P1-2:P40-39,P8-9:P33-32, 1:2.4 ±2%

P11-12:P30-29,P18-19:P23-22

RX P3-4:38-37,P6-7:P35-34, 1:1 ±2%

P13-14:P28-27,P16-17:P25-24

OCL (CHIP SIDE) 1.5mH typ

DCR (CHIP SIDE) 0.8Ω max

LL (CHIP SIDE) 0.5μH max

Cw/w 35pF max

ISOLATION 1,500Vrms



HALO/PBL

CALIFORNIA, USA
KOWLOON, HONG KONG
SINGAPORE

TITLE		SIGNATURES		DATE	REV.	DESC.	DATE
ISOLATION TRANSFORMERS		DRAWN PETER LU		2/5/07	A	FIRST ISSUE	2/5/07
FOR T1/E1		CHECKED LEI KEONG		2/5/07			
PART NO. TG91-S024NXRL		APPROVED PETER LU		2/5/07			
SCALE NONE	PAGE 1 OF 1	FILE TG91S024NXRL.DWG					