


Surface Mount Power

RC Series: carbon composition ($\frac{1}{4}$ & $\frac{1}{2}$ watt)
 RC Series: ceramic composition (above $\frac{1}{2}$ watt)
 RF Series: metal film
 RW Series: wirewound
 RP Series: power film
 RM Series: high voltage thick film



FEATURES

- Tolerance 1%, 5%, 10%, depending on construction
- Twelve wattage ratings
- Seven package sizes
- Two mounting designs to accommodate your soldering process
- Five power resistor technologies to optimize your operating performance:
 1. Carbon and Ceramic composition for surge and low inductance
 2. Metal film for high ohmic value and low T.C.
 3. Wire element for inrush current combined with low ohmic values. Resistance values as low as 0.005Ω
 4. Power film for high ohmic value and high wattage
 5. High Voltage thick film for high voltage applications
- Flexible J-bend terminations
- Working Temperature Range: -55°C to $+150^{\circ}\text{C}$



SERIES SPECIFICATIONS

Part Number	Power (watts)*	Maximum voltage	1% tol.	Resistance range 5% tol.	10% tol.	Temp. Coefficient 0.1Ω-1Ω -1Ω-10Ω 10Ω+	Dielectric Withstanding	Tape Size 330mm reels	Quantity per reel		
*RC0S2CA	0.25	250	—	—	2.2Ω-5.6M	—	±400	±400	1000V	16mm	1500
*RC0R5DB	0.50	350	—	—	2.2Ω-20M	—	±400	±400	1000V	24mm	1000
RW0S6BB	0.6	50	0.010Ω-1K	0.005Ω-1K		±90	±50	±20	1000V	12mm	2500
RF0S8BA	0.8	200	1Ω-5M	—		—	±100	±100	1000V	12mm	2000
RW1S0BA	1.0	50	0.005Ω-1K	0.005Ω-1K		±90	±50	±20	1000V	12mm	2000
RF1S0CA	1.0	350	10Ω-1M	1Ω-10M		—	±200	±100	1000V	16mm	1500
RC1R0EA	1.0	500	3.3-100K (10% tol only)					-1300	1000V	32mm	750
RP1S3CA	1.25	350	—	1Ω-1M		—	±250	±250	1000V	16mm	1500
RW1S5CA	1.5	75	0.005Ω-1.5K	0.005Ω-1.5K		±90	±250	±250	1000V	16mm	1500
RP1S5CB	1.5	350	—	1Ω-1M		—	±250	±250	1000V	16mm	1000
RP1R5CB											
RW2S0CB	2.0	100	0.005Ω-5K	0.005Ω-5K		±90	±50	±20	1000V	16mm	1000
RW2R0CB											
RP2S0DA	2.0	500	—	1Ω-1M		—	±250	±250	1000V	24mm	1000
RP2R0DA											
RW2S0DA	2.0	100	0.005Ω-5K	0.005Ω-5K		±90	±50	±20	1000V	24mm	1000
RW2R0DA											
RP2R5DB	2.5	500	—	1Ω-1M		—	±250	±250	1000V	24mm	1000
RW3R0DB	3.0	200	0.005Ω-13K	0.005Ω-13K		±90	±50	±20	1000V	24mm	1000
RP3R0EA	3.0	750	—	1Ω-1M		—	±250	±250	1000V	32mm	750
RW3R5EA	3.5	350	0.005Ω-25K	0.005Ω-25K		±90	±50	±20	1000V	32mm	750
RM0R7EA	0.75	2500	1KΩ-1000M	1KΩ-1000M		—	—	±50	1000V	32mm	750

*25°C ambient. E24 values standard; contact Ohmite for custom values.

*Discontinued


(continued)

Surface Mount Power


PERFORMANCE DATA

Construction	Temp. cycle (-55°C to 125°C, 1000 cycles)	Load Life (1000 hours at 25°C)	Immersion (260°C for 10 sec.)	Momentary Overload
RC Carbon/Ceramic Comp.	$\pm 4.0\% + .05\Omega$	$\pm 10.0\% + .05\Omega$	$\pm 3.0\% + .05\Omega$	6.3x rated power for 5 sec.
RF Metal Film	$\pm 0.5\% + .05\Omega$	$\pm 0.5\% + .05\Omega$	$\pm 0.1\% + .05\Omega$	2x rated power for 0.1 sec.
RW Wirewound	$\pm 0.5\% + .05\Omega$	$\pm 3.0\% + .05\Omega$	$\pm 0.1\% + .05\Omega$	5x rated power for 5 sec.
RP Power Film	$\pm 3.0\% + .05\Omega$	$\pm 5.0\% + .05\Omega$	$\pm 0.5\% + .05\Omega$	2x rated power for 0.1 sec.
RN Wirewound, Non-inductive	$\pm 0.5\% + .05\Omega$	$\pm 3.0\% + .05\Omega$	$\pm 0.1\% + .05\Omega$	5x rated power for 5 sec.
ALL models:	Leaching (260°C Solder immersion, 60 sec.)..... Thermal Shock (Units at -55°C, then rated power applied).. Flammability			No visible leaching No mechanical damage UL Material rating, UL94V0


Derating



TCR




Recommended Solder Profile



Preheating: 145°C $\pm 15^\circ$, max. 120 sec.

Soldering: min. 220°C, max. 60 sec.

Max. Temp.: 260°C $\pm 5^\circ$, 10 sec.
(RC only: 250°C $\pm 5^\circ$, 3 sec.)



The temperature rise graph data was obtained by a selection of test substrate size and trace width for each resistor size to limit operating temperatures to safe values.

The operating temperature safe rises are either 100°C substrate temperature rise or 180°C package hot spot temperature rise at 25°C ambient.

FR4: 0.062 in. thick; 0.062 in. traces

Alumina: 0.040 in. thick; 0.010 in. traces

Molding material rated at 205°C continuous.

RC SERIES: BAKE PROCEDURE

RC SERIES ONLY

A. Heat Treatment

110°C $\pm 10^\circ$ C
15 hours

B. Frequency of heat treatment

1 time only

C. Cautions


Solderability: may be affected due to oxidization of lead wire
Resistance value: some units may not completely recover to original value.

Soldering heat: some treated product may have substantial resistance change during soldering operation. It is recommended that parts be tested to evaluate soldering heat effects.

Surface Mount Power

DIMENSIONS

(mm/in.)



Package Outline Dimensions

Packages	A	B	C	D	G	I	J
BA (mm)	6.248±.508	3.454±.127	3.378 REF	2.794±.254	1.194 ±0.508	1.372±.305	3.454±.127
(in.)	0.246±.020	0.136±.005	0.133 REF	0.110±.010	0.047 ±0.020	0.054±.012	0.136±.005
CA (mm)	10.008±.508	4.039±.127	3.962 REF	5.588±.254	1.575 Nom.	1.626±.305	4.038±.127
(in.)	0.394±.020	0.159±.005	0.156 REF	0.220±.010	0.062 Nom.	0.064±.012	0.159±.005
CB (mm)	10.338±.508	5.74±.127	5.639 REF	6.604±.254	1.575 Nom.	2.134±.305	5.639±.127
(in.)	0.407±.020	0.226±.005	0.222 REF	0.260±.010	0.062 Nom.	0.084±.012	0.222±.005
DA (mm)	11.557±.508	6.096±.127	5.994 REF	6.604±.254	1.575 Nom.	2.921±.305	5.740±.127
(in.)	0.455±.020	0.240±.005	0.236 REF	0.260±.010	0.062 Nom.	0.115±.012	0.226±.005
DB (mm)	15.875±.508	6.934±.127	6.807 REF	10.592±.254	1.575 Nom.	2.921±.305	5.740±.127
(in.)	0.625±.020	0.273±.005	0.268 REF	0.417±.010	0.062 Nom.	0.115±.012	0.226±.005
EA (mm)	20.599±.508	6.934±.127	6.807 REF	14.529±.254	2.362 Nom.	2.921±.305	6.934±.127
(in.)	0.811±.020	0.273±.005	0.268 REF	0.572±.010	0.093 Nom.	0.115±.012	0.273±.005
BB (mm)	5.140±.508	2.54±.127	2.41 REF	2.00±.254	1.280 Nom.	1.640±.305	3.420±.127
(in.)	0.202±.010	0.10±.010	0.095 REF	0.079±.010	0.050 Nom.	0.065±.012	0.135±.005

PC Board Land Pattern

L	M	N	O	P
3.81	8.79	2.49	3.20	1.27
0.150	0.346	0.098	0.126	0.050
6.50	13.31	3.40	3.20	1.52
0.256	0.524	0.134	0.126	0.060
7.01	13.64	3.33	3.20	2.36
0.276	0.537	0.131	0.126	0.093
8.05	14.86	3.40	3.94	2.36
0.317	0.585	0.134	0.155	0.093
12.040	18.85	3.40	3.94	2.36
0.474	0.742	0.134	0.155	0.093
15.52	25.4	4.95	3.94	2.36
0.611	1.000	0.195	0.155	0.093
1.98	8.33	3.18	3.20	0.66
0.078	0.328	0.125	0.126	0.026

Note 1: Packages BA and CA are only available with a pedestal base. Packages CB and DA are available in either pedestal or recessed base.

Packages DB and EA are only available in a recessed base.


Note 2: Test point is .508mm (.020") above PCB.

Note 3: Tape and reel dimensions per EIA 481 A except "EA" size which is 12 mm component pitch versus 16mm pitch.

Land pattern dimensions are for reference only

Reel Dimensions

mm/(in.)




Size	A nom.	B	C max.	Quantity
12mm (0.472")	330mm (13")	12.4mm +2.0, -0.0 (0.488" +0.078, -0.00")	18.4mm (0.724")	2000 pcs. BA or 2500 pcs. BB
16mm (0.629")	330mm (13")	16.4mm +2.0, -0.0 (0.646" +0.078, -0.00")	22.4mm (0.882")	1500 pcs. CA or 1000 pcs. CB
24mm (0.944")	330mm (13")	24.4mm +2.0, -0.0 (0.961" +0.078, -0.00")	30.4mm (1.196")	1000 pcs. DA or DB
32mm (1.259")	330mm (13")	32.4mm +2.0, -0.0 (1.276" +0.078, -0.00")	38.4mm (1.52")	750 pcs. EA

All reels are compatible with major pick-and-place machines and made in accordance with EIA 481 A (except EA size, which is 12mm component pitch versus 16mm pitch).

(continued)

Surface Mount Power

ORDERING INFORMATION



(For example, the part number shown is a wire-wound resistor, 3.5 watt, recessed base, 32mm tape size, first case size [A], 1000 ohms 1% tolerance.)

Standard Part Numbers for Surface Mount Power Resistors

		Wirewound									
Package style	BA	CA	CB	CB	DA	DA	DB	EA	BB	EA	
Base: standard or recessed	S	S	S	R	S	R	R	R	S	R	
Wattage	1.0	1.5	2.0	2.0	2.0	2.0	3.0	3.5	0.6	1.0	
Ohmic value	Part No.										
Prefix	RW1S0BA, RW1S5CA, RW2S0CB, RW2R0CB, RW2S0DA, RW2R0DA, RW3R0DB, RW3R5EA, RW0S6BB, RC1R0EA										
Suffix	Tolerance suffix: F = 1% J = 5% K = 10%										
0.005	R005	J	J		F/J						
0.010	R010	F/J	J	J	F	J	J	J	F		
0.015	R015	F/J	J						F		
0.020	R020	J	J		F	J		J	F		
0.025	R025	J									
0.027	R027	J									
0.030	R030	F	J	J				J	F		
0.033	R033	J									
0.036	R036	J									
0.050	R050	F/J	J		J	F	J	J	F		
0.056	R056	J									
0.075	R075	J							F		
0.080	R080	J						J			
0.100	R100	F/J	J	J	F	J	J	J	F		
0.150	R150	J	J	J	J						
0.200	R200	J	J					J			
0.220	R220		J								
0.240	R240	J	J						F		
0.300	R300	J		J							
0.330	R330			J							
0.400	R040	J		J							
0.400	R400			J							
0.470	R470	J	J			J			F		
0.500	R500	J	J		J			J			
0.750	R750	J							F		
1.00	1R00	F/J	J	J		J	J		F		
2.00	2R00								F		

		Wirewound									
Package style	BA	CA	CB	CB	DA	DA	DB	EA	BB	EA	
Base: standard or recessed	S	S	S	R	S	R	R	R	S	R	
Wattage	1.0	1.5	2.0	2.0	2.0	2.0	3.0	3.5	0.6	1.0	
Ohmic value	Part No.										
Prefix	RW1S0BA, RW1S5CA, RW2S0CB, RW2R0CB, RW2S0DA, RW2R0DA, RW3R0DB, RW3R5EA, RW0S6BB, RC1R0EA										
Suffix	Tolerance suffix: F = 1% J = 5% K = 10%										
3.30	3R30									K	
4.70	4R70									K	
5.00	5R00								F		
5.60	5R60	J									
6.80	6R80									K	
7.50	7R50							J	F	K	
10.00	10R0	J	J			J			F	K	
15.00	15R0	J	J						F	K	
20.00	20R0		J								
22.00	22R0								F	K	
24.90	24R9								F		
33.00	33R0								F	K	
36.00	36R0								F		
47.00	47R0	J						J	F	K	
50.00	50R0										
51.00	51R0	J									
68.00	68R0									K	
82.00	82R0			J							
100.00	100R		J						F	K	
120.00	120R		J								
180.00	180R	J									
300.00	300R	J									
470.00	470R				J						
1K	1K00						J			K	
4.7K	4K70			J				J			
5K	5K00							J			