

LOCTITE ECI 5005 E&C

September 2022

PRODUCT DESCRIPTION

LOCTITE ECI 5005 E&C provides the following product characteristics:

Technology	Thermoplastic
Appearance	Gray liquid
Filler Type	Silver
Product Benefits	- Conductive - Screen printable
Cure	Heat cure
Application	Conductive Ink
Typical Assembly Applications	- Capacitive Switch - Resistive and capacitive touch pads - Electroluminescent lamps - ITO replacement

LOCTITE ECI 5005 E&C screen printable conductive ink is designed to leave a transparent conductive film when cured that can be used as a replacement for sputtered ITO film.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield , mPa·s (cP)	200
Solids Content, sample cured 30 minutes @ 150°C, %	2
Shelf Life @ 25°C (from date of manufacture), days	180
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Recommended Cure Schedule

3 minutes @ 85°C + 5 minutes @ 120°C

This material incorporates a two stage cure system. It is important for the printed inks to go directly into the oven after printing.

Parts racked and left out of the oven before curing will tend to separate and "fisheye", showing a non-uniform looking finish.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Adhesion on PET substrate, Cross Hatch, grade	5B
Haze, Spectrometer, %	<1.3
Transmission, Spectrometer, @ 550 nm, %	>92

Electrical Properties

Sheet Resistance on PET substrate, 4-point probe, ohms/sq	<100
---	------

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

- LOCTITE ECI 5005 E&C is supplied ready for use and does not require dilution.
- Mix material prior to use. There may be soft settling in container that needs to be brought back into suspension before use.
- Mix thoroughly with plastic spatula or mechanical stirrer from bottom of container , careful not to whip air into the product. Using a plastic spatula will decrease the possibility of introducing plastic grindings from the container sidewalls into the product, which could damage the screen.

APPLICATION

- Pour enough ink on the screen to last approximately 10 minutes of printing at a time. Adding more will cause excess solvent evaporation on the screen, affecting the coating thickness as well as the transparency.
- A number of factors including screen mesh size, squeegee material and emulsion thickness influence the dried film's thickness, final resistance and transparency.
- Recommended screen printing parameters are:

Screen Type	Polyester or stainless steel
Screen Mesh	305
Emulsion Thickness , µm	10 to 40
Squeegee Type	Polyurethane
Squeegee Hardness, durometer	70 to 80
Print Speed, inches/second	15

Not for product specifications

The technical data contained herein are intended as



reference only. Please contact your local Henkel representative for assistance and recommendations on the specifications of this product.

CLEAN-UP

The equipment can be cleaned with Isopropanol and Acetone.

STORAGE

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 0°C. Storage below -20°C or above 30 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.



Conversions

$$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$$

$$\text{kV/mm} \times 25.4 = \text{V/mil}$$

$$\text{mm} / 25.4 = \text{inches}$$

$$\text{N} \times 0.225 = \text{lb/F}$$

$$\text{N/mm} \times 5.71 = \text{lb/in}$$

$$\text{N/mm}^2 \times 145 = \text{psi}$$

$$\text{N/mm}^2 = \text{MPa}$$

$$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$$

$$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$$

$$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$$

$$\text{mPa}\cdot\text{s} = \text{cP}$$

Reference 1

