

LOCTITE EDAG PF 021 E&C

September 2014

PRODUCT DESCRIPTION

LOCTITE EDAG PF 021 E&C provides the following product characteristics:

Technology	Thermoplastic
Appearance	clear
Operating Temperature-Maximum	204°C
Product Benefits	• Fast UV cure • Prevents silver migration • Physically protects SMD • Process ease • Dot dispensable
Cure	Ultraviolet (UV) light
Application	Encapsulant
Key Substrates	Polyester, Polycarbonate film and FR-4

LOCTITE EDAG PF 021 E&C encapsulating photopolymer is designed to secure low profile surface mount devices (SMD) to rigid or flexible substrates. It is particularly effective for use as a physical and environmental protection of the mounted device.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Solids Content by Weight, %	100
Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):	
Speed 5 rpm	11,500
Theoretical coverage, sq ft/gal:	
@ 10 µm coating thickness	1,600
Shelf Life @32°C, year	1
(from date of qualification in original seal)	
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Recommended UV Cure

Light Dose, Joule/cm² 0.4 to 1.0

For thicknesses >2.0 mils, a longer wavelength bulb is required e.g. Fusion "D". UV measurements were made with an EIT radiometer.

Percent Volatiles

VOC, g/l	0
----------	---

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore A	80
Pencil hardness	2B
Elongation, %	176

Electrical Properties

Dielectric Constant, ASTM D150-87	3.24
Dielectric Strength, ASTM D149-91, volts	750

TYPICAL PERFORMANCE OF CURED MATERIAL

Tensile Strength	N/mm ² 7.58	(psi) (1,100)
------------------	------------------------	---------------

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Mixing/Dilution

- Product is ready for use but should be mixed thoroughly using a plastic spatula. (Syringe-packed material needs no mixing).
- Mix smoothly from bottom of container, being careful not to whip air into the product.

2. Application

- LOCTITE EDAG PF 021 E&C should be applied in a glob over the entire surface of small devices, or along the outside leads of large devices.
- Its viscosity is designed to conform to the device and flow out over the substrate just prior to UV curing.
- Dot dispensing equipment should be selected based on the exact application, i.e., device size and production speed.

3. Cleanup

- Uncured resin may be cleaned with Isopropanol, cellosolve acetate and similar solvents.

Storage

Store product in the unopened container in a cool dry well ventilated area. Storage information may be indicated on the product container labeling.

Optimal Storage: 32°C. Storage below 32°C or greater than 32°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} = \text{N/mm}^2$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana,**S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1