

LOCTITE® SI 5092™

Known as LOCTITE® 5092™
November 2015

PRODUCT DESCRIPTION

LOCTITE® SI 5092™ provides the following product characteristics:

Technology	Silicone
Chemical Type	Alkoxy silicone
Appearance (uncured)	Yellow to green liquid ^{LMS}
Fluorescence	Positive under UV light ^{LMS}
Components	One component - requires no mixing
Cure	Ultraviolet (UV) light
Secondary Cure	Moisture for shadowed areas
Application	Potting, Coating or Sealing
Self-leveling	Uniform cavity fill
Flexibility	Highly flexible. Enhances load bearing & shock absorbing characteristics of the bond area.
Specific Benefit	Non-corrosive
Strength	Medium

LOCTITE® SI 5092™ is used for potting, coating and sealing of various automotive, electronic, military and industrial components.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C	0.99
Solids/Non-Volatile Content, %	>95
Flash Point - See SDS	
Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP):	
Spindle 3, speed 10 rpm	4,000 to 7,500 ^{LMS}

TYPICAL CURING PERFORMANCE

Normal processing conditions will include exposure to sufficient UV light irradiance to effectively cure the material. Surface and/or atmospheric moisture will promote the cure of material in shadowed regions. Although functional strength is developed almost instantly due to the UV curing nature of LOCTITE® SI 5092™, increased cure properties are developed during 72 hours at ambient conditions.

Surface Cure

When curing with sufficient UV light irradiance, exposed material cures dry to the touch in seconds. Atmospheric moisture cures material not exposed to UV light.

Tack Free Time, seconds:

Electrodeless, D bulb:

75 mW/cm² ,	270 to 600
250 mW/cm² ,	75 to 90

Electrodeless, H bulb:

75 mW/cm² ,	60 to 75
250 mW/cm² ,	20 to 30

Zeta® 7200:

75 mW/cm² ,	≤90 ^{LMS}
250 mW/cm² ,	10 to 20


Skin Over Time, minutes:

Moisture cure only	≤300 ^{LMS}
--------------------	---------------------


Depth of Cure


Shadowed areas rely on surface and/or atmospheric moisture to effect cure. Depth of cure is limited to approximately 6 millimeters and will take at least 24 hours to develop. Rapid depth of cure can be attained with focused UV light. The graph(s) below show the depth of cure obtained up to 60 seconds at two different levels of UV irradiance.

Curing System: Zeta® 7200



Curing System: Electrodeless, H bulb



Curing System: Electrodeless, D bulb**TYPICAL PROPERTIES OF CURED MATERIAL**

Cured @ 70 mW/cm², measured @ 365 nm, for 60 seconds per side plus 7 days @ 25 °C / 50% RH

Physical Properties:

Coefficient of Thermal Expansion, ISO 11359-2, K ⁻¹	460×10 ⁻⁶
Water Absorption, %	0.6
Water Vapor Trans. Rate, ASTM E96, g/(h·m²)	60.08
Shrinkage, %	1.4
Shore Hardness, ISO 868, Durometer A:	
22 °C control	42
Aged @ 150 °C for 24 hours	44
Aged @ 260 °C for 24 hours	50

Elongation, ISO 37, %:

22 °C control	75
Aged @ 150 °C for 24 hours	75
Aged @ 260 °C for 24 hours	41

Tensile Strength, ISO 37:

22 °C control	N/mm² 1.6 (psi) (230)
Aged @ 150 °C for 24 hours	N/mm² 1.9 (psi) (275)
Aged @ 260 °C for 24 hours	N/mm² 0.9 (psi) (130)
Tear Strength, ISO 34-1, Die B	N/mm 2 (lb./in.) (11)

Electrical Properties:

Volume Resistivity, IEC 60093, Ω·cm	64×10 ¹²
Dielectric Breakdown Strength, IEC 60243-1, kV/mm	22
Dielectric Constant / Dissipation Factor, IEC 60250:	
100 Hz	3.179 / 0.0045
100 kHz	3.175 / 0.0045

Cured @ 75 mW/cm², for 60 seconds per side plus 7 days @ 25 °C / 50% RH

Physical Properties:

Shore Hardness, ISO 868, Durometer A	32 to 50 ^{LMS}
Elongation, ISO 37, %	≥75 ^{LMS}
Tensile Strength, ISO 37	N/mm² ≥0.6 ^{LMS} (psi) (≥87)

Cured @ 180 mW/cm², for 30 seconds per side

Physical Properties:

UV Depth of Cure, mm	≥2 ^{LMS}
----------------------	-------------------

TYPICAL PERFORMANCE OF CURED MATERIAL

Cured @ 70 mW/cm², for 60 seconds, plus 7 days post UV Cure @ 25 °C / 50% RH, (samples with 0.25 mm gap)

Shear Strength

Lap Shear Strength, ISO 4587:

Aluminum to Glass	N/mm² 0.52 (psi) (75)
Steel to Glass	N/mm² 0.63 (psi) (90)
Glass to Glass	N/mm² 1.52 (psi) (220)
Polybutylene Terephthalate (PBT) DR51 to Glass	N/mm² 1.14 (psi) (165)
Tin(bright) to Glass	N/mm² 1.26 (psi) (183)
Tin(dull) to Glass	N/mm² 1.33 (psi) (193)
Brass to Glass	N/mm² 1.28 (psi) (185)
Amodel® AS-1566 to Glass	N/mm² 1.74 (psi) (252)
Amodel® A-1133 to Glass	N/mm² 1.67 (psi) (242)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use:

1. For best performance bond surfaces should be clean and free from grease.
2. The product is designed to be initially cured with UV light at a minimum irradiance of 70 mW/cm² for approximately 20 seconds, increased exposure may be required for curing deeper sections.
3. Functional strength is achieved almost instantly.
4. Full performance properties will develop over 72 hours.
5. Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
6. Excess material can be easily wiped away with non-polar solvents.

Loctite Material Specification^{LMS}

LMS dated October 02, 2002. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 2 °C to 8 °C. Storage below 2 °C or greater than 8 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.6

Henkel Americas
+860.571.5100

Henkel Europe
+49.89.320800.1800

Henkel Asia Pacific
+86.21.2891.8859

For the most direct access to local sales and technical support visit: www.henkel.com/industrial