

# LOCTITE® SI 5293

April 2025

## Product description

LOCTITE® SI 5293 provides the following product characteristics:

<b>Technology</b>	Silicone
Chemical type	Alkoxy silicone
Appearance (uncured)	Transparent amber to yellow liquid
Fluorescence	Positive under UV light
Components	One component - requires no mixing
<b>Cure</b>	Ultraviolet (UV) light
Secondary Cure	Moisture for shadowed areas
<b>Application</b>	Conformal coating

LOCTITE® SI 5293 is designed to provide environmental protection for printed circuit boards and other sensitive electronic components.

## Typical properties of uncured material

Specific gravity @ 25°C	1.0
Flash point - see SDS	
Viscosity, Brookfield - RVT, 25, °C Spindle 1, speed 10 rpm	400 to 800
Solids/non-volatile content, %	≥85

## Typical curing performance

LOCTITE® SI 5293 cures when exposed to UV radiation of 365nm. Normal processing conditions will include exposure to sufficient UV light irradiance to effectively cure the material. Surface and/or atmospheric moisture will promote the cure of material in shadowed regions. Although functional strength is developed almost instantly due to the UV curing nature of LOCTITE® SI 5293 increased cure properties are developed during 72 hours at ambient conditions.

## Surface cure

Tack free time, hours	
Cured @ 22 °C / 50±5 % RH	10 to 24

## Typical properties of cured material

Cured @ 70 mW/cm<sup>2</sup>, for 60 seconds per side using a glass filtered metal halide light source plus 7 days @ 22 °C / 50±5% RH.

## Physical properties

Coefficient of thermal expansion, ISO 11359-2, K <sup>-1</sup>	300×10 <sup>-6</sup>
Coefficient of thermal conductivity ISO 8302, W/(m·K)	0.18
Glass transition temperature ISO 11359-2, °C	-40
Water vapor trans. rate, ASTM E96, method A, g/(h·m <sup>2</sup> )	1.23 to 1.37

## Electrical properties

Volume resistivity, IEC 60093, Ω·cm	1×10 <sup>14</sup>
Dielectric breakdown strength, IEC 60243-1, kV/mm	16
Dielectric constant / Dissipation factor, IEC 60250	
100 Hz	4.6 / 0.005
1 kHz	4.1 / 0.006
1 MHz	4.5 / 0.014

Cured @ 70 mW/cm<sup>2</sup>, for 60 seconds per side

## Physical properties

Shore Hardness, ISO 868, Durometer OO	60 to 90
UV Depth of cure, mm	≥1.3
Elongation, at break, ISO 37, %	15

## Physical properties

Tensile strength, ISO 37	N/mm <sup>2</sup> (psi)	0.4 (60)
--------------------------	----------------------------	-------------

## GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

## Directions for use

1. For best performance bond surfaces should be clean and free from grease.
2. The product is designed to be initially cured with UV light at a minimum irradiance of 70 mW/cm<sup>2</sup> for approximately 20 to 40 seconds, increased exposure may be required for curing deeper sections.
3. Functional strength is achieved almost instantly.
4. Full performance properties will develop over 72 hours.
5. Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
6. Excess material can be easily wiped away with non-polar solvents.

## Loctite material specification<sup>LMS</sup>

LMS dated February-24, 1997. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.



**Storage**

Store product in the unopened container in a dry location. Storage information may be indicated on the product package labeling.

**Optimal storage: 8 to 28 °C. Storage below 8°C or greater than 28°C can adversely affect product properties.**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\mu\text{m} / 25.4 = \text{mil}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{N/mm}^2 \times 145 = \text{psi}$   
 $\text{MPa} \times 145 = \text{psi}$   
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb-in}$   
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb-ft}$   
 $\text{N-mm} \times 0.142 = \text{oz}\cdot\text{in}$   
 $\text{mPa}\cdot\text{s} = \text{cP}$

**Disclaimer**

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3