

LOCTITE® 4310™

September 2020

PRODUCT DESCRIPTION

LOCTITE® 4310™ provides the following product characteristics:

Technology	Cyanoacrylate/UV
Chemical Type	Ethyl cyanoacrylate with photoinitiator
Appearance	Transparent, light yellow-green to dark blue-green liquid
Fluorescence	Positive under UV light
Components	One part - requires no mixing
Cure	Ultraviolet (UV) / Visible light
Secondary Cure	Humidity
Application	Bonding
Key substrates	Plastics, rubbers and metals

LOCTITE® 4310™ is designed for bonding applications that require very rapid fixturing, fillet cure or surface cure. The UV light cure properties facilitate rapid curing of exposed surface areas thereby minimizing blooming and providing an alternative to solvent borne accelerators. Suitable for use in the assembly of **disposable medical devices**.

ISO-10993

LOCTITE® 4310™ has been tested to Henkel's test protocols based on ISO-10993 biocompatibility standards, as a means to assist in the selection of products for use in the medical device industry.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25°C 1.06

Flash Point - See SDS

Viscosity, Cone & Plate, mPa·s (cP):


Physica MC100, Cone MK 22, shear rate 100 s⁻¹ 100 to 250

TYPICAL CURING PERFORMANCE


Primary Cure Mechanism, UV

Depth of Cure

Electrodeless, D bulb, 100 mW/cm², measured @ 365 nm



LED Flood Array 405nm, 100 mW/cm², measured @ 405nm



Tack Free Time / Surface Cure

Tack Free Time is the time in seconds required to achieve a tack free surface

UV/Visible light sources

Electrodeless, H bulb

30 mW/cm², measured @ 365 nm ≤10

Zeta® 7411-S

30 mW/cm², measured @ 365 nm ≤5

CUREJET 405 LED

65 mW/cm², measured @ 365 nm ≤5

LED Flood Array 405nm

65 mW/cm², measured @ 365 nm ≤5



Cure Speed vs. Substrate

The rate of cure will depend on the substrate used. The table below shows the fixture time achieved on different materials at 22 °C / 50% relative humidity. This is defined as the time to develop a shear strength of 0.1 N/mm². Fixture time measurements relate to non-UV cure.

Fixture time, seconds

ABS	<5
Aluminum (grit blasted)	5 to 15
Neoprene	15 to 25
Phenolic	250 to 290
Polycarbonate	10 to 20
Polyethylene	>300
Polyethylene (Primer 770)	5 to 10
Polypropylene	>300
Polypropylene (plasma treated)	270 to 300
PVC	90 to 105
Steel (degreased)	20 to 30

TYPICAL PROPERTIES OF CURED MATERIAL

Cured @ 100 mW/cm², measured @ 365nm, for 30 seconds per side using an Electrodeless system, D bulb.

Physical Properties

Coefficient of Thermal Expansion, ISO 11359-2, K ⁻¹	
Pre Tg	56×10 ⁻⁶
Glass Transition Temperature, ASTM E 228, °C	102
Shore Hardness, ISO 868, Durometer D	84
Linear Shrinkage, in/in	6
Water Absorption, ISO 62, %	
2 hours in boiling water	2.2
7 days in water @ 22 °C	1.3
Elongation, at break, ISO 527-3, %	7.3
Tensile Strength, ISO 527-3	N/mm ² (psi)
Tensile Modulus, ISO 527-3	N/mm ² (psi)

TYPICAL PERFORMANCE OF CURED MATERIAL**Adhesive Properties**

Cured @ 30 mW/cm², measured @ 365 nm, for 10 seconds using a Zeta® 7400 light source

Block Shear Strength, ISO 13445:

Polycarbonate	N/mm ² (psi)	≥9.0 (≥1,305)
---------------	----------------------------	------------------

Cured @ 100 mW/cm², measured @ 365 nm, for 30 seconds using a Zeta® 7411-S light source

Block Shear Strength, ISO 13445:

Acrylic to Acrylic	N/mm ² (psi)	14.4 (2,090)
Polycarbonate to Polycarbonate	N/mm ² (psi)	22 (3,190)
Polycarbonate to Steel (grit blasted)	N/mm ² (psi)	12 (1,740)

Cured @ 100 mW/cm², measured @ 405 nm, for 30 seconds using a LED Flood Array 405nm

Block Shear Strength, ISO 13445:

Acrylic to Acrylic	N/mm ² (psi)	10.6 (1,540)
Polycarbonate to Polycarbonate	N/mm ² (psi)	16.4 (2,380)
Polycarbonate to Steel (grit blasted)	N/mm ² (psi)	12.6 (1,830)

Cured @ 1,000 mW/cm², for 10 seconds using an Electrodeless system, D bulb

Needle Pullout Strength:

Material	22	Gauge cannula	27	Gauge cannula
Polycarbonate	N (lb)	139 (31)	N (lb)	38 (9)
Polyethylene	N (lb)	11 (2)	N (lb)	24 (6)
Polyethylene (plasma treated)	N (lb)	128 (27)	N (lb)	53 (12)
Polypropylene	N (lb)	24 (5)	N (lb)	18 (4)
Polypropylene (plasma treated)	N (lb)	87 (20)	N (lb)	41 (9)

Cured for 24 hours @ 22°C (non-UV cure)

Lap Shear Strength, :

Steel (grit blasted)	N/mm ² (lb/in)	20.4 (2,950)
----------------------	------------------------------	-----------------

Block Shear Strength, ISO 13445:

Acrylic to Acrylic	N/mm ² (psi)	8 (1,160)
Polycarbonate to Polycarbonate	N/mm ² (psi)	6 (870)
Polycarbonate to Steel (grit blasted)	N/mm ² (psi)	10.4 (1,510)



Cured for 48 hours @ 22°C (non-UV cure)

180° Peel Strength, ISO 8510-2:

Steel (grit blasted)	N/mm ² (lb/in)	3 (17)
----------------------	------------------------------	-----------

TYPICAL ENVIRONMENTAL RESISTANCECured @ 30 mW/cm², measured @ 365 nm, for 10 seconds.


Block Shear Strength, ISO 13445:

Polycarbonate

Heat Aging

Aged at temperature indicated and tested @ 22 °C.

* Note: Substrate failure for all test specimens*

**Chemical/Solvent Resistance**

Aged under conditions indicated and tested @ 22 °C.

* Note: Substrate failure for all test specimens*

Environment	% of initial strength				
	°C	24 h	100 h	500 h	1000 h
Water	22	100	100	100	100
95% RH	40	100	100	100	100
Heptane	22	100	100	100	100
Isopropanol	22	100	100	100	100

Thermal Stability of Needle Assemblies

Aged @ 60°C and tested @ 22 °C

Needle pullout strength, % of initial strength **4 weeks** **8 weeks**

Polycarbonate

22 Gauge Cannula	65	50
27 Gauge Cannula	90	90

Polypropylene (plasma treated)

22 Gauge Cannula	70	80
27 Gauge Cannula	75	70

Sterilization Resistance of Needle Assemblies

Sterilized as indicated and tested @ 22 °C

Needle Pullout Strength, % of initial strength:

	Gamma	ETO	Autoclave	
	30 kGy	1 Cycle	1 Cycle	5 Cycles
Polypropylene (plasma treated)				
22 Gauge Cannula	50	55	40	45
27 Gauge Cannula	65	60	70	70

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use:

1. This product is light sensitive; exposure to daylight, UV light and artificial lighting should be kept to a minimum during storage and handling.
2. For best performance bond surfaces should be clean and free from grease.
3. Excess adhesive can be dissolved with Loctite cleanup solvents, nitromethane or acetone.

Product specification:

The technical data contained herein are intended as reference only and are not considered specifications for the product. Product specifications are located on the Certificate of Analysis or please contact Henkel representative.

Data ranges

The data contained herein may be reported as a typical value. Values are based on actual test data and are verified on a periodic basis.

Temperature/Humidity Ranges: 23°C / 50% RH = 23±2°C / 50±5% RH

Approval and certificate

Please contact Henkel representative for related approval or certificate of this product.



Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 kV/mm x 25.4 = V/mil
 mm / 25.4 = inches
 $\mu\text{m} / 25.4 = \text{mil}$
 N x 0.225 = lb
 N/mm x 5.71 = lb/in
 N/mm² x 145 = psi
 MPa x 145 = psi
 N·m x 8.851 = lb-in
 N·m x 0.738 = lb-ft
 N·mm x 0.142 = oz-in
 mPa·s = cP

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal storage: 2°C to 8°C. Storage below 2°C or greater than 8°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Reference 0.4