



LOCTITE® ECI 8060HV

March 2025

PRODUCT DESCRIPTION

LOCTITE® ECI 8060HV provides the following product characteristics:

Technology	Thermoplastic
Appearance	Black paste
Filler type	Carbon
Operating temperature, °C	Max. 70°C
Cure	Hot air drying or infrared
Application	Conductive ink
Product benefits	• Screen printable • Flexible • Printable on most common substrates • Rapid heating with well-defined cut-off temperature, no external control devices needed • Self-regulation temperature ~60°C
Typical assembly applications	Self-regulating heating elements used for higher voltage applications (100-220V)
Key substrates	PET, PEN, PI

LOCTITE® ECI 8060HV is a positive temperature coefficient (PTC) ink for the creation of high voltage heating elements (100-250 V). It is screen printable and has a PTC ratio above 15. LOCTITE® ECI 8060HV is often used for printing self-regulating heating elements onto polyester foil with a self-regulating temperature of ~60°C. Furthermore, it is compatible with the silver ink LOCTITE® ECI 1010. LOCTITE® ECI 8060HV is blendable with non-conductive ink LOCTITE® NCI 8002 for resistance adjustment.

TYPICAL PROPERTIES OF UNDRIED MATERIAL

Solid content, (box oven, 1hour @ 150°C), %	51
Density, g/cm ³	1.0
Viscosity, Rheometer, @25°C, mPa·s (cP)	
Shear rate 1.5 s ⁻¹	55,000
Thixotropic index, (1.5/15 s ⁻¹)	4.0
Theoretical coverage, m ² /kg	
@ 10 µm coating thickness	46
Shelf life @ 8 to 28°C, days	365

TYPICAL DRYING PERFORMANCE

Recommended drying cycle
10 minutes @ 140°C

LOCTITE® ECI 8060HV can be dried using forced air or infrared systems. Higher temperatures for longer time exposure will improve the performance. Care should be taken with infrared. Too much energy can destroy the coating.

Design drying rates for the maximum the substrate and production speeds can tolerate.

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF THE DRIED MATERIAL

Physical properties

Adhesion on PET, ASTM 3359, grade 5B


Electrical properties

Sheet resistance, 4-point probe, Ohm/sq/25µm
10 minutes @ 140°C 39,000

PTC ratio 23

Resistance vs. Temperature

PTC Ratio vs. Temperature curve of dried PTC-ink, measured on a test design. The PTC ratio is calculated by $PTC\ Ratio(T) = R(T)/R(25^{\circ}C)$



GENERAL INFORMATION

Please consult the Safety Data Sheet (SDS) for safe handling information of this product.

Directions for use

Detailed on-boarding process, including in-depth design, processing, and testing guidelines are available. Starting with a test plan to explore the influence of different design parameters is highly recommended. You can reach out to your Henkel representative for more information.

1. Design guidelines

PTC carbon ink should be printed as small resistors, all in parallel connection, and connected by highly conductive silver ink.

To design a PTC self-regulating heater, you should at least know:

- Targeted self-regulation temperature
- Working voltage
- Initial power
- Heater dimensions
- Environmental condition and integration

The main design parameters are

- PTC Ink. Defines the self-regulation temperature.
- Busbars width. To be adjusted to the maximum inrush current to avoid over heating.
- Silver spacing. To be adjusted to reach self-regulation at the working voltage.
- Number of PTC element and aspect ratio (silver spacing/width). They are adjusted to match the targeted power and heat distribution.

2. Surface preparation

Surfaces to be coated must be clean, dry and free of dust.

3. Mixing/Dilution

- LOCTITE® ECI 8060HV is supplied ready for use.
- Should dilution be necessary, use butyl glycol acetate (CAS: 112-07-2). Henkel recommends a maximum of 10 wt%. This should be accomplished by adding solvent at 0.5 wt% intervals until desired viscosity and printability is achieved.
- If needed, the product sheet resistance can be increased by adding LOCTITE® NCI 8002 up to 30 wt%.

Weight ratio ECI 8060HV / NCI 8002	Sheet resistance (Ohm/sq/25µm)
100/0	39,000
97.5/2.5	43,000
95/5	51,000
92.5/7.5	59,000
90/10	79,000
85/15	83,000
80/20	93,000
70/30	229,000

- Blending with LOCTITE® NCI 8002 should be performed with a mechanical propeller mixer for the entire jar volume. Avoid rapid stirring as this causes air entrapment.
- After long time storage, a gel type viscosity may be observed. Mix thoroughly, preferentially using a mechanical propeller mixer at low speed, before use to ensure it is homogeneous.

4. Application

Recommended screen and printing parameters are

Screen type

Polyester screen, mesh/cm	51
Stainless steel screen, mesh/cm	180
Dry coating thickness, µm	22
Emulsion, solvent resistant, µm	10 to 40
Squeegee shore hardness	70 to 90

5. Electrical circuit protection

- For electrical insulation and environmental protection, a layer on top of the PTC ink should be added. This layer will affect the resistance of the PTC ink, up to 50% increase, but should not cause long term drift.
- Different solutions are available:
 - UV-dielectrics LOCTITE® EDAG 456 and LOCTITE® EDAG PF-455B are compatible with PTC carbon inks.
 - Pressure sensitive adhesives, also known as tapes, to bond a protective foil. High purity adhesives without tackifiers are preferred.
 - Printable adhesives printed around the PTC elements to bond a protective foil.

Storage

Store product in the unopened container in a cool dry well ventilated area. Storage information may be indicated on the product container labeling.

Optimal storage: 8 to 28°C. Storage below 8°C or above 28°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.



Conversions
 $(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$
Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3