



LOCTITE® ECCOBOND UF 3808

January 2025

PRODUCT DESCRIPTION

LOCTITE® ECCOBOND UF 3808 provides the following product characteristics:

Technology	Epoxy
Appearance	Black liquid
Components	One-component
Product benefits	• High Tg • Low CTE • Reworkable • Halogen free • One component • Room temperature flow capability • Fast cure at moderate temperatures • Compatible with most Pb-free solders • Stable electrical performance in temperature humidity bias
Cure	Heat cure
Application	Underfill
Typical assembly applications	Chip scale packages and BGA

LOCTITE® ECCOBOND UF 3808 capillary underfill is designed to cure quickly at low temperatures to minimize stress to other component. When cured, this material provides excellent mechanical properties to protect solder joints during thermal cycling.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Physica, CP50-1, mPa·s (cP):	
@ 1,000 s ⁻¹	348
Specific gravity	1.16
Pot life @ 25°C, (25% viscosity increase), days	3
Shelf life @ -20°C, days	365
Flash point - see SDS	

TYPICAL CURING PERFORMANCE

Cure schedule
≥8 minutes @ 130°C
Alternative curing conditions
5 minutes @ 150°C

The above cure profiles are guideline recommendations. These conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical properties	
Coefficient of thermal expansion, ppm/°C:	
Below Tg	55
Above Tg	171
Glass transition temperature (Tg) by TMA, °C	113
Storage modulus, DMA	
@25°C	N/mm ² 2,610
	(psi) (379,000)
Electrical properties	
Dielectric constant / Dissipation factor @ 23°C	
@ 1 GHz	3.19 / 0.0099
@ 2 GHz	3.24 / 0.0088

GENERAL INFORMATION
Please consult the Safety Data Sheet (SDS) for safe handling information of this product.

- Thawing
1. Typical thaw times are listed as follows:
 - 1 hour for 10 cc syringes
 - 1.5 hours for 30 cc syringes
 - 2 to 3 hours for 55 cc syringes
 2. Allow container to reach room temperature before use.
 3. After removing from the freezer, set the syringes to stand vertically while thawing.
 4. DO NOT open the container before contents reach 25°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
 5. DO NOT re-freeze. Once thawed, the adhesive should not be re-frozen.

- Direction for use
1. Thawed material should immediately be placed on dispense equipment for use.
 2. If the adhesive is transferred to a final dispensing reservoir, care must be exercised to avoid entrapment of contaminants and/or air into the adhesive.
 3. Adhesive must be completely used within the product's recommended work life.



Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal storage: -25 to -15°C. Storage above -15°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 4