

## LOCTITE® EDAG 423SS

April 2025

### PRODUCT DESCRIPTION

LOCTITE® EDAG 423SS provides the following product characteristics:

<b>Technology</b>	Thermoplastic
<b>Appearance</b>	Dark gray
<b>Operating temperature</b>	105°C
<b>Product benefits</b>	<ul style="list-style-type: none"> <li>• Applicable with manual, semi-automatic and high speed reel-to-reel screen printing equipment</li> <li>• Excellent screen residence time</li> <li>• Non-critical, flexible low temperature drying cycles</li> <li>• Excellent adhesion to polyester film</li> <li>• Compatible for use with polyester film, polycarbonate film, PVC film, paper and cardboard</li> </ul>
<b>Cure</b>	Hot air drying
<b>Application</b>	Conductive ink
<b>Typical assembly applications</b>	Membrane touch switches, Printed resistors, Keyboards, Heating elements, Flexible circuits, Membrane switches and Protection against electrostatic discharge (ESD)
<b>Key substrates</b>	PET, PEN, PI, PVC, Paper

LOCTITE® EDAG 423SS is a conductive carbon ink, which is often used for printing contact areas, protect silver tracks from oxidation. LOCTITE® EDAG 423SS is screen printable and compatible with a large range of silver inks LOCTITE® EDAG 479SS, LOCTITE® EDAG 725A, LOCTITE® ECI 1010.

### TYPICAL PROPERTIES OF UNDRIED MATERIAL

Solids content, %	36
Viscosity, Brookfield RVT, 20°C, after 15 minutes, mPa·s (cP)	
Speed 20 rpm	23,000
Density, g/cm <sup>3</sup>	1.1
Theoretical coverage, wet product, m <sup>2</sup> /kg	
at 10µm dry coating thickness	20
Shelf life at 5 to 30°C, (package type dependent), days*	≥ 365
Flash point, DIN 53213, °C	78

\*For additional information, contact your Henkel representative

### TYPICAL SCREEN PRINTING PROCESS

#### Printing equipment type

- Manual
- Semi-automatic
- High speed reel to reel

#### Recommended screen type

Monofilament polyester screen, threads/cm	61 to 90
Stainless steel screen, threads/cm	77 to 110

#### Recommended screen type

Polyurethane, Durometer	70 to 75
-------------------------	----------

#### Emulsion thickness

Emulsion thickness, µm	20 to 40
------------------------	----------

#### Applied dry coating thickness

Applied dry coating thickness, µm	6 to 10
-----------------------------------	---------

#### TYPICAL DRYING CYCLE

##### Recommended drying cycle

Conventional air circulated oven  
30 minutes at 90°C

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

#### TYPICAL PROPERTIES OF DRIED MATERIAL

Dry Coating on polyester film dried 30 minutes at 90°C

#### Physical properties

Adhesion on PET, ASTM D3359, grade	5B
------------------------------------	----

#### Electrical properties

Sheet resistance, 4-point probe, Ohm/sq/25µm	
30 min at 90°C	33
15 min at 120°C	37

#### GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

## Directions for use

1. LOCTITE® EDAG 423SS is supplied ready for use.
2. Should dilution be necessary, use dbutyl glycol acetate (CAS: 112-07-2). Henkel recommends a maximum of 10 wt%. This should be accomplished by adding solvent at 5 wt% intervals until desired viscosity and printability is achieved.
3. Mix thoroughly before use to ensure the entire ink volume is homogenous. A slow speed propeller may be utilized to mix until product is uniform. Avoid rapid stirring as this causes air entrapment.
4. If a gel structure forms after extended storage, the product may be warmed slightly in a water bath (not exceeding 65°C) and stirred.

## Clean up

The screen and equipment can be cleaned with dilution solvent, or esters (butylacetate, propylacetate, or ethylacetate), or ketones (MEK, Acetone), or similar solvents.

## Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal storage: 5 to 30°C. Storage below 0°C or greater than 40°C can adversely affect product properties.**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

## Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

## Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\mu\text{m} / 25.4 = \text{mil}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{N/mm}^2 \times 145 = \text{psi}$   
 $\text{MPa} \times 145 = \text{psi}$   
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$   
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$   
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$   
 $\text{mPa}\cdot\text{s} = \text{cP}$

## Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.



**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 5