

## LOCTITE® SI 5910®

Known as LOCTITE® 5910  
January 2019**PRODUCT DESCRIPTION**

LOCTITE® SI 5910® provides the following product characteristics:

<b>Technology</b>	Silicone
Chemical Type	Oxime silicone
Appearance (uncured)	Black paste <sup>LMS</sup>
Components	One component - requires no mixing
Viscosity	Thixotropic paste
Cure	Room temperature vulcanizing (RTV)
Application	Sealing
Specific Benefits	Excellent resistance to automotive engine oils.

Typical applications include stamped sheet metal covers (timing covers and oil sumps) where good oil resistance and the ability to withstand high joint-movement is required. The thixotropic nature of LOCTITE® SI 5910® reduces the migration of liquid product after application to the substrate.

**TYPICAL PROPERTIES OF UNCURED MATERIAL**

Specific Gravity @ 20 °C 1.34

Flash Point - See SDS


Extrusion Rate, g/min:

Pressure 0.62 MPa, time 15seconds, temperature 25 °C:  
Semco Cartridge 300 to 650<sup>LMS</sup>**TYPICAL CURING PERFORMANCE****Surface Cure**

Tack Free Time, minutes:


Cured @ 25 °C / 50±5 % RH ≤40<sup>LMS</sup>**Cure Speed**

The graph below shows shear strength developed with time on Aluminum lapshears at a bond gap of 0.5 mm. Cure condition 23±2 °C, 60±5% RH. Strength is determined according to ISO 4587.

**Depth of Cure**

The depth of cure depends on temperature and humidity. Depth of cure was measured on strip pulled from a ramped PTFE mold (maximum depth 10 mm).

The graph below shows the increase in depth of cure with time at 23±2 °C / 50±5 % RH.

**TYPICAL PROPERTIES OF CURED MATERIAL**

Cured for 1 week @ 25°C / 50±5 % RH

**Physical Properties:**

Shore Hardness, ISO 868, Durometer A	30
Elongation, ISO 37, %	≥400 <sup>LMS</sup>
Tensile Strength, ISO 37	N/mm <sup>2</sup> ≥1.7 <sup>LMS</sup> (psi) (≥247)
Tensile Strength, at 100% elongation, ISO 37	N/mm <sup>2</sup> 0.6 to 1.0 (psi) (87 to 145)

**Electrical Properties:**

Volume Resistivity, IEC 60093, $\Omega \cdot \text{cm}$	$1.69 \times 10^{14}$
Surface Resistivity, IEC 60093, $\Omega$	$2.81 \times 10^{16}$
Dielectric Constant / Dissipation Factor, IEC 60250:	
1 kHz	4.53 / 0.019
100 kHz	4.09 / 0.009
1 MHz	4.05 / 0.008
10 MHz	4.08 / 0.017

Cured for 21days @  $23 \pm 2^\circ\text{C}$  /  $60 \pm 5\%$  RH, 2 mm thick film  
Tensile strength, ISO 37, N/mm $^2$  (Elongation, at break, %):

Environment	100 h	500 h	1000 h
22 °C	1.7(700)	2.4(600)	1.9(560)
150 °C	2.2(400)	2.2(450)	2.3(470)
175 °C	2.2(380)	2.1(350)	1.4(330)
200 °C	2.2(370)	2.0(340)	1.4(300)
5W40 oil, 120 °C	1.9(520)	2.3(490)	2.1(590)
Motor oil, 150°C	1.9(520)	1.8(450)	2.6(600)
Water/glycol	1.0(620)	0.6(540)	0.9(570)

**TYPICAL PERFORMANCE OF CURED MATERIAL****Adhesive Properties**After 21 days @  $23^\circ\text{C}$  /  $60 \pm 5\%$  RH and 0.5 mm gap

Lap Shear Strength :

Mild steel	N/mm $^2$ (psi)	0.9 to 1.4 (130 to 200)
Aluminum 2024-T3	N/mm $^2$ (psi)	0.6 to 1.4 (90 to 200)
Alclad	N/mm $^2$ (psi)	1 to 1.6 (145 to 230)
Zinc dichromate	N/mm $^2$ (psi)	1 to 1.6 (145 to 230)



**TYPICAL ENVIRONMENTAL RESISTANCE**Cured for 21days @  $23^\circ\text{C}$  /  $60 \pm 5\%$  RH

Lap Shear Strength :

Alclad

**Hot Strength**

Tested at temperature

**Heat Aging**Aged at temperature indicated and tested @  $22^\circ\text{C}$ **Environmental Aging - Effect on bulk properties****GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

**Directions for use**

1. For best performance bond surfaces should be clean and free from grease.
2. Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
3. The bond should be allowed to cure (e.g. seven days), before subjecting to heavy service loads.
4. Excess material can be easily wiped away with non-polar solvents.
5. For full automatic applications a volumetric dispensing system is recommended.

**Loctite Material Specification<sup>LMS</sup>**

LMS dated January 08, 2009. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

**Storage**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.** Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.



**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 kV/mm x 25.4 = V/mil  
 mm / 25.4 = inches  
 $\mu\text{m} / 25.4 = \text{mil}$   
 N x 0.225 = lb  
 N/mm x 5.71 = lb/in  
 N/mm<sup>2</sup> x 145 = psi  
 MPa x 145 = psi  
 N·m x 8.851 = lb·in  
 N·m x 0.738 = lb·ft  
 N·mm x 0.142 = oz·in  
 mPa·s = cP

**Disclaimer**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons

against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.13

