


## Specification for LED Driver Series

**AB-D65240-V12-Q**

**AB-D65240-V24-Q**

**AB-D67240-V12-Q**

**AB-D67240-V24-Q**



### Features:

- Universal AC input / Full range (Max 305VAC)
- Built-in active PFC function
- IP65/IP67, Metal Case, Suitable for dry, humid, and rainy environments
- Protections: Short circuit / Over Voltage / Over Temperature
- Adopt metal shell and internal glue filling, which can be used in dangerous situations
- Built-in lightning protection device can meet the requirements of DM 4KV / CM 6kV
- Compliance with worldwide safety regulations for lighting
- 5 years warranty

### Description:

AB-D6x240-Vxx-Q series is an outdoor waterproof power supply featuring dual mode constant voltage and constant current output for IP65 and constant voltage only for IP67. Its input voltage range is 90-305Vac, with a high efficiency of up to 94%, fanless design, working in the temperature range of - 40 ° C to + 60 ° C under free air convection. It has an ultra-high power factor, ultra-low total harmonic distortion, and low standby power consumption, with all-around protection functions such as lightning protection and waterproof function, which not only greatly improves the product's reliability but also ensure the product's life cycle. This series is designed for LED lighting such as road lighting, floodlights, stage lighting, advertising lights, etc., suitable for almost all kinds of applications where LED lamps can be installed. The product is designed completely in accordance with the world's lighting equipment safety regulations to ensure the safety of both the user and the luminaire system during installation.

**Model**

Model	Rated Output Voltage	Rated Output Current	Min. Output Voltage CC Mode	Maximum Output Power	Current Tolerance	Total Harmonic Distortion (Typ.)	Power Factor (Typ.)	Efficiency (Typ.)
AB-D65240-V12-Q	12V	9-18A	7.2V	216W	±5%	4%	0.98	92%
AB-D67240-V24-Q	24V	5-10A	14.4V	240W	±5%	4%	0.98	93%

Model	Mode	IP Grade
AB-D65240-Vxx-Q	Constant Voltage and Constant Current	IP65
AB-D67240-Vxx-Q	Constant Voltage Only	IP67

**Remark:**

All parameters NOT specifically mentioned are measured at 230VAC input, full load, and 25 °C of ambient temperature.

**Naming System:**
**AB-D65240-V12-Q**

65: IP65  
240: 240 Watts  
V12: 12 Volts  
Q: No Dimming

**AB-D67240-V12-Q**

67: IP67  
240: 240 Watts  
V12: 12 Volts  
Q: No Dimming

**AB-D65240-V24-Q**

65: IP65  
240: 240 Watts  
V24: 24 Volts  
Q: No Dimming

**AB-D67240-V24-Q**

67: IP67  
240: 240 Watts  
V24: 24 Volts  
Q: No Dimming

## Input

Parameter	Minimum Value	Typical Value	Maximum Value	Note
Rated Input Voltage	100Vac		277Vac	The derating curve is shown in the figure
Input Voltage	90Vac		305Vac	
Input Frequency	47Hz		63Hz	
Maximum Input Current			2.3A	110Vac, Full Load
			1.2A	230Vac, Full Load
Input Inrush Current			65A	230Vac/50Hz, Cold Start
Power Factor	0.97	0.98		230Vac, Full Load
Total Harmonic Input		4%	5%	230Vac, Full Load
Leakage Current			0.7mA	230Vac/50Hz, Full Load
Stand-By Power Consumption		0.35W	0.5W	230Vac/50Hz, No Load

## Output

Parameter	AB-D6x200-V12-Q	AB-D6x200-V24-Q	Note
Output Voltage Adjusted Range	10.5-13.5VDC	22-26VDC	Maximum Output power should comply to: $P_o = V_o * I_o = 240W$
The Minimum Output Voltage (CC Mode)	7.2V	14.4V	
Rated Output Current	18A	10A	
Output Current Adjusted Range	9-18A	5-10A	
Rated Output Power	216W	240W	
Rated Output Efficiency	92%	93%	230Vac
Output Current Tolerance		±5%	
Output Voltage Ripple (PK-PK)		±2%	Full Load (Test under 20M bandwidth)
Output Current Ripple (PK-PK)		±5%	
Rise Time	100ms		230Vac
Startup Time	300ms		230Vac
Line Regulation		±1%	Full Load
Load Regulation		±1%	

## Characteristic Curve

Fig.1 Output Load-Temperature Curve:




Fig.2 Static Characteristic Curve:




Fig.3 I-V Curve:




Fig.4 Efficiency-Load Curve:




Fig.5 Power Factor Characteristics Curve (PF):





Fig.6 Total Harmonic Distortion Curve (THD):



## Protection

Parameter		Conditions	Note
Protection	Overload	1.1-1.6 times of rated load	Auto-recovery after overload removed
	Short Circuit	Short circuit power ≤ 0.5W	Hiccup mode, auto-recovery after short circuit removed
	Over Voltage	1.5 times of rated output voltage	Auto-recovery after overvoltage removed
	Over Temperature	110°C	Auto-recovery after over temperature removed

## Environment Requirement


Parameter	Minimum	Typical	Maximum	Note
Working Temperature	-40°C	25°C	+60°C	See Fig.2
Storage Temperature	-40°C	25°C	+85°C	
Working Humidity	10%RH		90%RH	
Storage Humidity	5%RH		95%RH	
IP Grade			IP67	
Cooling Mode	Natural Cooling			

## Safety & EMC Standard

Certificate	Safety Standards		Certification	Note
UL/CUL	UL8750			
TUV	EN61347-1:2015 EN 61347-2-13:2014+A1 EN62493:2015			
SAA	AS/NZS 61347.2.13			
CCC	GB 19510.14-2009			
CE	EN 61347-2-13:2014 +A1 EN61347-1:2015			
Safety Test	Technical Indexes		Note	
Dielectric Strength	Input-Output	3200Vac/5mA Max/60s	Reinforced insulation, no breakdown, no flashover	
	Primary to Safety (Ground AC To FG)	1600Vac/5mA Max/60s	Basic insulation, no breakdown, no flashover	
	Secondary to Safety (Ground DC To FG)	1000Vac/5mA Max/60s	Functional insulation, no breakdown, no flashover	
Insulation Resistance	Input-Output	$\geq 10M\Omega$	Test voltage: 500Vdc	
Ground Resistance		$\leq 0.1\Omega$	25A/1min	
Leakage Current		$\leq 0.75mA$	277Vac	
EMC Test	Standard		Criterion	
Conduction CE	EN55015			
Radiation RE	EN55015			
Harmonics	EN IEC 61000-3-2		Class C	

## Others

Parameter	Condition	Note
Lifetime	55,000 Hours	230Vac, Full Load, TC: 75°C
MTBF	200,000 Hours	230Vac, Full Load, Ta: 25°C (MIL-HDBK-217F)
TC	90°C	
Warranty	5 Years	TC: 75°C
Weight	900g	
Dimensions	220.6*62.5*41.3mm	L x W x H

**Mechanical Specification (Unit: mm)**

**Remark:**

AC Input Cable:	VDE, H05RN-F 105°C 3G*1.0mm <sup>2</sup> , L=300mm+SR Yellow-green: PE, Brown: L, Blue: N
DC Output Cable:	12V: SJTW, 14AWG/ 2*2.08mm <sup>2</sup> 105°C, L=300mm+SR White : V+, Black : V- 24V: SJTW, 16AWG/2*1.31mm <sup>2</sup> 105°C, L=300mm+SR White : V+, Black : V- & H05RN-F 2*1.0mm <sup>2</sup> , 105°C L=300mm+SR red : V+, black : V-