

Precision Thin Film Chip Resistors



Electronics

PFC Series



Features:

- High stability tantalum nitride film
- Available in 0402, 0603, 0805 and 1206
- TCR to $\pm 10\text{ppm}/^\circ\text{C}$
- Sulfur resistant to ASTM B809-95
- Both Pb-free and SnPb finish available
- AEC-Q200 qualified



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)


Electrical Data

		PFC0402	PFC0603	PFC0805	PFC1206
Power rating (@70°C)	mW	50	100	250	333
Rated operating voltage (not to exceed $\sqrt{(\text{PxR})}$)	V		75	100	200
Resistance range	ohms	40R to 35K	40R to 100K	10R to 267K	10R to 1MΩ
Tolerance	%		0.05, 0.1, 0.25, 0.5, 1, 2, 5		
TCR	ppm/ $^\circ\text{C}$			10, 15, 25, 50, 100	
ESD withstand ¹ (HBM)	kV	0.5	1	1.5	2
Noise	dB			<-25	
Operating temperature	°C			-65 to 150	
Values				E24 or E192	

Note 1: This product is not considered ESD-sensitive for packaging and handling purposes.

Physical Data

Dimensions in inches / (mm) and weight in mg						
Size	L	W	H	a	b	Wt. nom.
0402	0.04 ±0.003 (1.02 ±0.08)	0.021 ±0.005 (0.53 ±0.13)	0.012 ±0.003 (0.3 ±0.08)	0.01 ±0.006 (0.25 ±0.15)		0.55
0603	0.063 ±0.004 (1.6 ±0.1)	0.031 ±0.004 (0.79 ±0.1)	0.02 ±0.006 (0.51 ±0.15)	0.012 ±0.008 (0.3 ±0.2)	0.015 ±0.009 (0.38 ±0.23)	1.97
0805	0.081 ±0.006 (2.06 ±0.15)	0.05 ±0.007 (1.27 ±0.18)		0.015 ±0.009 (0.38 ±0.23)	0.016 ±0.008 (0.41 ±0.2)	4.48
1206	0.126 ±0.008 (3.2 ±0.2)	0.063 ±0.005 (1.6 ±0.13)	0.024 ±0.006 (0.61 ±0.15)	0.025 ±0.017 (0.64 ±0.43)		8.93



Note: For PCB mounting pad recommendations see:

<https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Application-Note/TN006-Recommended-Layouts-for-SMD-Resistors.pdf>

Construction

Conductors and tantalum nitride resistive element are applied to an alumina substrate. The product is laser trimmed to value, and a protective epoxy coat is applied. The product is then metallized and plated to provide a wrap-around solderable termination with a 100% matte tin or an SnPb finish on a nickel barrier layer. It is 100% tested then packed in carrier tape. Pb-free parts use paper carrier tape, whilst SnPb parts use plastic carrier tape.

Marking

0402 size and values which are neither E24 nor E96 are not marked. 0603 is marked with three characters and 0805 and 1206 with four characters. See <https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Application-Note/TN004-Methods-for-Marking-Values-on-Resistors.pdf>.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT Electronics plc

BI Technologies IRC Welwyn


www.ttelectronics.com/resistors



Performance Data

Test per MIL-PRF-55342	$\pm\Delta R/R\%$	
	Typical	Maximum
Thermal shock	0.02	0.1
Low temperature operation	0.01	0.05
Short-time overload	0.01	0.05
High temperature exposure	0.03	0.1
Effects of solder	0.01	0.1
Moisture resistance	0.03	0.1
Life	0.03	0.1
Sulfuration test: ASTM B809 (modified) 105°C, dry, 1000 hours	0.02	0.05

Temperature Derating



Ordering Procedure

Global Part Number Example: PFC0402LFD1002BT10 (0402, 25ppm/°C at 10 kilohms $\pm 0.1\%$, Pb-free)

P	F	C	0	4	0	2	L	F	D	1	0	0	2	B	T	1	0
1			1	2		3	4		5		6		7				

1 Series	2 Size	3 Termination ¹	4 TCR (ppm/°C)	5 Value	6 Tolerance	7 Packing		
						Packing		
PFC	0402	LF = Pb-free (100%Sn)	T = ± 10	3 digits + multiplier	A = $\pm 0.05\%$	Pb-free (LF) product		
	0603	PB = SnPb (60/40) (0603, 0805, 1206 only)	Y = ± 15	R = ohms for values <100 ohms	B = $\pm 0.1\%$	T10	0402	10,000/reel
	0805		D = ± 25		C = $\pm 0.25\%$	T5	0603, 0805, 1206	5000/reel
	1206		C = ± 50		D = $\pm 0.5\%$	T1	All sizes ²	1000/reel
			Z = ± 100		F = $\pm 1\%$	SnPb (PB) product		
					G = $\pm 2\%$	T1	0603, 0805, 1206	1000/reel
					J = $\pm 5\%$			

Note 1: Terminations are anti-sulfur as standard.


Note 2: Non-standard packing option – consult factory for availability.



Legacy Part Numbers

This product has two legacy part number formats. These are still available for ordering, but for new designs use of the Global Part Number is recommended.

European Legacy Part Number: W1206R-01-1K0BI (1206, 100ppm/°C, 1 kilohm ±0.1%, Pb-free)



1 Series	2 Size	3 Option ¹	4 TCR (ppm/°C)	5 Value	6 Tolerance	7 Termination & Packing		
W = PFC	0402	R Anti-sulfur AS Blank -02 = ±50 -01 = ±100	-12 = ±10	E24/E96 = 3/4 characters R = ohms K = kilohms M = megohms	A = ±0.05%	I	All sizes	Pb-free, Standard pack
	0603		-11 = ±15		B = ±0.1%	PB	0603, 0805, 1206	SnPb finish, 1000/reel
	0805		Blank = ±25		C = ±0.25%	Standard Pack		
	1206		-02 = ±50		D = ±0.5%	0402		10,000/reel
			-01 = ±100		F = ±1%	0603, 0805, 1206		5000/reel
					G = ±2%			
						J = ±5%		

Note 1: Terminations are anti-sulfur as standard.

USA Legacy Part Number: PFC-W1206LF-01-1001-B (1206, 100ppm/°C, 1 kilohm ±0.1%, Pb-free)



1 Series	2 Model	3 Termination ¹		4 TCR (ppm/°C)	5 Value	6 Tolerance	Standard Packing	
PFC	W0402	LF All sizes ASLF R 0603, 0805, 1206	Anti-sulfur & Pb-free (100%Sn) Anti-sulfur & SnPb (60/40)	12 = ±10	3 digits + multiplier R = ohms for values <100 ohms	A = ±0.05%	0402	10,000/reel
	W0603			11 = ±15		B = ±0.1%	0603, 0805,	Pb-free 5000/reel
	W0805			03 = ±25		C = ±0.25%	1206	SnPb 1000/reel
	W1206			02 = ±50		D = ±0.5%		
				01 = ±100		F = ±1%		
						G = ±2%		
						J = ±5%		

Note 1: Terminations are anti-sulfur as standard.