



NOTES:

1. MATERIALS:
BODY - BRASS, NICKEL PLATED
CONTACTS - BRASS, NICKEL PLATED

C INSULATOR - PA66 GF30
HEX NUT - DIE CAST, NICKEL PLATED

2. HEX NUT TO BE SHIPPED ASSEMBLED TO THE BODY OF JACK.

B 3. MOUNTING HOLE - $\phi 0.437$ [11.10] ± 0.005 [0.13]

4. THIS PART IS RoHS COMPLIANT.

PART NUMBER	CENTER PIN DIAMETER
721AFMS	0.083 [2.1mm]
712AFMS	0.098 [2.5mm]

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.
					UNLESS OTHERWISE SPECIFIED	SIZE
					1. ALL DIMENSIONS IN INCHES [mm]	WIDTH
					- TWO PLACE DECIMALS ± 0.02 [0.5]	MULT
					- THREE PLACE DECIMALS ± 0.005 [0.13]	LBS/M
C	28757	07/29/25	PC	TJK		TEMPER
B	28300	06/23/20	PC	TJK	FINISH	
A	27939	9/6/17	TJK	TJK	SPEC No.	MATERIAL
REV	ECO NUMBER	DATE	BY	APVD	FIRST USED ON	SPEC No.
					DATE DRAWN	SCALE
					8/28/17	3:1
					BY	APVD
					TJK	TJK
					8/28/17	8/28/17
					NAME	
					FRONT MOUNT SHIELDED	PART No.
					POWER JACK, RoHS	712AFMS_721AFMS
						REV
						C
REVISIONS					DO NOT SCALE DRAWING	