

Customer Part:

Description

- Standard 7.0 x 5.0mm crystal oscillator in a ceramic package with a seam sealed metal lid, hermetically sealed.
- Model CFPS-72
- Model Issue number 16



Frequency Parameters

- | | |
|-------------------------------|--------------------|
| ■ Frequency | 18.4320MHz |
| ■ Frequency Stability | ±100.00ppm |
| ■ Operating Temperature Range | -40.00 to 85.00°C |
| ■ Ageing | ±5ppm per year max |



Electrical Parameters

- Supply Voltage 5.0V ±10%
- Current Draw 35.000mA
- Note: parameters are referenced to 15pF load

Output Details

- Output Compatibility CMOS
- Drive Capability 15pF typ, 30pF max
- Rise and Fall Time 10.0ns max
- Duty Cycle 40/60
- Start up time: 10ms max, 1.1ms typ to 90% of final amplitude (under ideal conditions @25°C).

Output Control

- **Standby Operation:**
Logic '1' (>70% Vs) to pad 1 enables oscillator output.
Logic '0' (<30% Vs) to pad 1 disables oscillator output; the oscillator output goes to the high impedance state.
No connection to pad 1 enables oscillator output.
Standby Current: 10µA max, 2.3µA typ @25°C.

Environmental Parameters

- Shock: Half Sine shock pulse with peak acceleration 500g; Pulse duration: 0.3ms
- Vibration: MIL-STD-202 Method 204. 5g for 20 minutes, 12 cycles in each of the 3 orientations, 10 - 2000 Hz. As per Table 11 of AEC-Q200.
- Storage Temperature Range: -55 to 125°C


Manufacturing Details

- RoHS Terminations NiAu
- RoHS Reflow Temp 260°C 10s max


Compliance

- | | |
|------------------------------|----------------|
| ■ RoHS Status (2015/863/EU) | Compliant |
| ■ REACH Status | Compliant |
| ■ MSL Rating (JDEC-STD-033): | Not Applicable |

Outline (mm)



Recommended Solder Pad Layout

**Sales Office Contact Details:**

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.igdfrequencyproducts.com


Customer Part:

Packaging Details


- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape.

Standard Pack Quantity: 1,000

Test Circuit



Waveform



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com