

Customer Part:



Description

- Surface mount 3.2 x 2.5mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.
- Model: CFPS-41
- Model Issue number: 7

Frequency Parameters

- Frequency: 27.0MHz
- Frequency Stability: $\pm 50.00\text{ppm}$
- Operating Temperature Range: -40.00 to 85.00°C
- Ageing: $\pm 3\text{ppm}$ max per year @ 25°C

Electrical Parameters

- Supply Voltage: $1.8\text{V} \pm 5\%$
- Current Draw: 6.000mA

Output Details

- Output Compatibility: CMOS
- Drive Capability: 15pF max
- Rise and Fall Time: 6.0ns max
- Duty Cycle: 40/60
- Output Low VoL : 10% V_s max
- Output High VoH : 90% V_s min

Output Control

- Standby Operation:
Logic '1' ($>70\%$ V_s) to pad 1 enables oscillator output
Logic '0' ($<30\%$ V_s) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state
No connection to pad 1 enables oscillator output
Standby Current: $10\mu\text{A}$ max
- Start-Up Time: 10ms max

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Shock: MIL-STD-883F: 2002.4. Condition B, 1500g, 0.5ms, 1/2 sine wave.
- Vibration: MIL-STD-883F: 2007.3, Test Condition: Peak acceleration: 20g Frequency range: (20Hz ~ 2000Hz), Peak to peak amplitude: 1.52mm , Sweep time: 20 minute/axis, Pendicular total test time: 4 hours.

Manufacturing Details


- RoHS Terminations: Ni, Au
- RoHS Reflow Temp: 260°C max for 30 seconds max

Compliance


- RoHS Status (2015/863/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable



Outline (mm)



Test Circuit



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com


Web: www.iqdfrequencyproducts.com

Customer Part:


Packaging Details

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape
- Standard Pack Quantity: 3,000

Test Circuit



Wave Form



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com