

Customer Part:



Description

- Surface mount 3.2 x 2.5mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.
- Model CFPS-40
- Model Issue number 8

Frequency Parameters

- Frequency 25.0MHz
- Frequency Stability $\pm 50.00\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Ageing $\pm 3\text{ppm}$ max per year @ 25°C

Electrical Parameters

- Supply Voltage 2.5V $\pm 5\%$
- Current Draw 8.000mA

Output Details

- Output Compatibility CMOS
- Drive Capability 15pF max
- Rise and Fall Time 5.0ns max
- Duty Cycle 40/60
- Output Low Vol: 10% Vs max
Output High Voh: 90% Vs min
- Start-Up Time: 10ms max
- Output Low Vol: 10% Vs max
Output High Voh: 90% Vs min
- Start-Up Time: 10ms max
- Output Low Vol: 10% Vs max
Output High Voh: 90% Vs min
- Start-Up Time: 10ms max
- Output Low Vol: 10% Vs max
Output High Voh: 90% Vs min
- Start-Up Time: 10ms max
- Output Low Vol: 10% Vs max
Output High Voh: 90% Vs min
- Start-Up Time: 10ms max

Output Control

- Standby Operation:
Logic '1' ($>70\%$ Vs) to pad 1 enables oscillator output
Logic '0' ($<30\%$ Vs) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state
No connection to pad 1 enables oscillator output
Standby Current: 10 μA max

Environmental Parameters


- Storage Temperature Range: -55 to 125°C
- Drop Test: in accordance with JIS-C0044; The specimen is measured for its frequency before the test. It is then dropped from a height of 75cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness.
- Vibration: MIL-STD-883F : 2007.3, Test Condition: Peak acceleration:20g Frequency range;(20Hz~2000Hz), Peak to peak amplitude: 1.52mm, Sweep time: 20 minute/axis, Pendicular total test time: 4 hours

Manufacturing Details


- RoHS Terminations NiAu
- RoHS Reflow Temp 260°C max for 30s max



Outline (mm)



Test Circuit



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com

Customer Part:

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details


- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on
cut tape

Standard Pack Quantity: 3,000

Test Circuit



Wave Form



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com