

## Customer Part:



### Description

- Standard 1.6 x 1.2mm crystal oscillator in a hermetically sealed ceramic package with a seam sealed metal lid.
- Model IQXO-640
- Model Issue number 4

### Frequency Parameters

- Frequency 12.0MHz
- Frequency Stability  $\pm 50.00\text{ppm}$
- Operating Temperature Range  $-40.00$  to  $85.00^\circ\text{C}$
- Ageing  $\pm 5\text{ppm max/yr @ } 25^\circ\text{C}$

### Electrical Parameters

- Supply Voltage  $3.3\text{V} \pm 10\%$
- Current Draw  $4.000\text{mA}$

### Output Details

- Output Compatibility CMOS
- Drive Capability  $15\text{pF max}$
- Rise and Fall Time  $4.5\text{ns max}$
- Duty Cycle  $45/55\%$
- Output Voltage Low (Vol):  $10\%V_s$  max
- Output Voltage High (Voh):  $90\%V_s$  min

### Output Control

- Standby Operation:  
Logic '1' ( $\geq 70\%V_s$ ) to pad 1 enables oscillator output.  
Logic '0' ( $\leq 30\%V_s$ ) to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state.  
No connection to pad 1 enables oscillator output.
- Standby Current:  $10\mu\text{A max}$

### Environmental Parameters

- Storage Temperature Range:  $-55$  to  $125^\circ\text{C}$
- Shock: IEC 60068-2-27:  $1000\text{g}$ ,  $1\text{ms}$ , 3 times in each of 3 mutually perpendicular planes.
- Vibration: IEC 60068-2-6:  $1.5\text{mm}$  amplitude,  $10\text{Hz}$ - $55\text{Hz}$ ,  $1\text{min}$  in 3 mutually perpendicular planes, duration  $2\text{hrs}$  each plane (total  $6\text{hrs}$ ).


### Manufacturing Details

- RoHS Terminations W( $15 \pm 4\mu\text{m}$ ), Ni( $8 \sim 20\mu\text{m}$ ), Au( $0.2 \sim 260 \pm 5^\circ\text{C}$  for  $5\text{s max}$ )


### Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

### Outline (mm)



### Test Circuit



### Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)



## Crystal Clock Oscillator Specification

Part No. + Packaging: **LFSPX0059847**

---

Customer Part:

### Packaging Details

■

Standard Pack Quantity:

---

#### Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)