

Customer Part:

Description

- LVDS output SMD crystal oscillator
5 x 3.2mm ceramic package with a hermetically sealed metal lid
- Model IQXO-741
- Model Issue number 2

Frequency Parameters

- Frequency 100.0MHz
- Frequency Tolerance INCLUSIVE
- Frequency Stability $\pm 25.00\text{ppm}$
- Operating Temperature Range 0.00 to 70.00°C
- Ageing $\pm 3\text{ppm}$ max per year @ 25°C

Electrical Parameters

- Supply Voltage 2.5V $\pm 5\%$
- Current Draw 66.000mA
- Start up time: 10ms max

Output Details

- Output Compatibility LVDS
- Drive Capability 100 Ω
- Rise and Fall Time 0.7ns max
- Duty Cycle 45/55%
- Output Voltage Logic Low: 1.43V typical, 1.6V max
Output Voltage Logic High: 1.1V typical, 0.9V min
- Output Differential Voltage: 247mV to 454mV max, 350mV typical
- Output Offset Voltage: 1.125V to 1.375V max, 1.2V typical

Output Control

- Logic '1' to pad 1 (70%Vs min) enables oscillator outputs
Logic '0' to pad 1 (30%Vs max) disables oscillator outputs,
oscillator outputs go to the high impedance state
No connection to pad 1 enables oscillator outputs

Noise Parameters

- Phase Jitter (12kHz to 20MHz): 1ps rms max

Environmental Parameters


- Storage Temperature Range: -55 to 125°C
- Drop: 120cm drop (3 times) onto hard wooden board
- Vibration: MIL-STD-883, Method 2007, Test Condition A:
10Hz-55Hz-10Hz, 1.5mm amplitude, full sine, 2mins per cycle,
3 mutually perpendicular planes, 2hrs duration in each plane

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable



Outline (mm)



Test Circuit



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com



Customer Part:

Packaging Details

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape

Standard Pack Quantity: 1,000

Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com