

Customer Part:



Description

- 1.6 x 1.2mm crystal oscillator in a ceramic package with a seam sealed metal lid, hermetically sealed.
- Model IQXO-985
- Model Issue number 1

Frequency Parameters

- Frequency 32.7680kHz
- Frequency Stability $\pm 30.00\text{ppm}$
- Operating Temperature Range -20.00 to 70.00°C
- Frequency Stability: Includes Frequency Tolerance @ 25°C , operating temperature range, supply voltage variation and load variation.

Electrical Parameters

- Supply Voltage $2.5\text{V} \pm 10\%$
- Current Draw (typical) 0.025mA

Output Details

- Output Compatibility CMOS
- Drive Capability 15pF max
- Rise and Fall Time 200.0ns max
- Duty Cycle 45/55
- Output Voltage Levels:
Output Low (VoL): $10\%V_{\text{S}}$ max
Output High (VoH): $90\%V_{\text{S}}$ min
- Start Up Time: TBD

Output Control

- Stand-by Mode:
Logic '0' ($30\%V_{\text{S}}$ max) to pad 1 disables the oscillator output, the output goes to a high impedance state.
Logic '1' ($70\%V_{\text{S}}$ min) or no connection to pad 1 enables oscillator output.
- Stand-by Current: $1.4\mu\text{A}$ typical $3\mu\text{A}$ max

Environmental Parameters

- Storage Temperature Range: -40 to 85°C


Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable


Packaging Details

■


Standard Pack Quantity:



Outline (mm)



Test Circuit



* Inclusive of jigging and equipment capacitance

Sales Office Contact Details:


UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com

Customer Part:

Wave Form



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com