

Customer Part:



Description

- Surface mount Voltage Controlled Temperature Compensated Oscillator (VCTCXO) providing a high degree of frequency stability over a wide temperature range in a hermetically sealed ceramic package
- Model CFPT-126
- Model Issue number 6

Frequency Parameters

- Frequency 32.7680MHz
- Frequency Stability $\pm 0.50\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Ageing $\pm 1\text{ppm}$ typical in 1st year @ 25°C
- Frequency Stability Reference to $(F_{\text{max}} + F_{\text{min}})/2$

Electrical Parameters

- Supply Voltage 3.3V $\pm 5\%$
- Current Draw (Typical): 3mA @ 20MHz
- Supply Voltage Variation: <30MHz $\pm 0.3\text{ppm}$
30MHz to 40MHz $\pm 0.4\text{ppm}$
- Load Variation: $\pm 0.2\text{ppm}$ (@15pF $\pm 10\%$)
After Reflow: $\pm 1.0\text{ppm}$

Frequency Adjustment

- Pulling $\pm 5\text{ppm}$ min
- Control Voltage 1.65V $\pm 1.0\text{V}$

Output Details

- Output Compatibility HCMOS
- Drive Capability 15pF nom
- Rise and Fall Time 8.0ns max
- Duty Cycle 45/55%

Environmental Parameters

- Shock: IEC 60068-2-27, Test Ea: 980m/s² acceleration for 6ms, 3 shocks in each of 3 mutually perpendicular planes
- Vibration: IEC 60068-2-6, Test Fc, Procedure B4: 10Hz-60Hz 1.5mm displacement, 60-2000Hz at 98.1m/s², 30mins in 3 mutually perpendicular planes at 1 oct/min
- Solderability: MIL-STD-202, Method 208, Category 3
- Storage Temperature Range: -55 to 125°C

Manufacturing Details


- Soldering: Suitable for Convection Reflow soldering. Peak temperature 260°C, 60sec max above 220°C
- Washing: Able to withstand aqueous washing
- RoHS Terminations NiCoAu
- RoHS Reflow Temp 260degC 10s

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): 1



Outline (mm)



Test Circuit



* Inclusive of probe and jig capacitance

Sales Office Contact Details:

UK: +44 (0)1460 270200


Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com


Customer Part:**Packaging Details**

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on
cut tape

Standard Pack Quantity: 1,000

Test Circuit

* Inclusive of probe and jig capacitance

Wave Form**Sales Office Contact Details:**

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com