

QUARTZ CRYSTAL MHZ

Part Number: 830105822101 | -B | CFPX-228


AKA Number: LFX TAL058221




General Information

Standard 6 x 3.5mm crystal available only in a 4 pad package.
Ceramic package with a seam sealed metal lid, hermetically sealed.

Dimensions [mm]



Recommended Land Pattern [mm]



QUARTZ CRYSTAL MHZ



Part Number: 830105822101 | -B | CFPX-228
AKA Number: LFX TAL058221

Frequency Parameters

Frequency	12.0 MHz
Frequency Tolerance	± 30 ppm
Frequency Stability	± 30 ppm
Operating Temperature	-40 °C to 85 °C
Overtone Order	Fundamental
Ageing	± 3 ppm max per year @ 25 °C

Material Parameters

Moisture Sensitivity Level (MSL)	Not Applicable
----------------------------------	----------------

Manufacturing Details

260°C max for 10s max

Company Address

IQD Frequency Products Ltd.
Station Road
Crewkerne
Somerset
TA18 8AR, United Kingdom

Electrical Parameters

Load Capacitance C_L	20 pF
Shunt Capacitance C₀	7 pF max.
ESR	30 Ω max.

Environmental Parameters

Storage Temperature Range:	-55 °C to 125 °C
■ Drop Test: Unit dropped from height of 100cm onto hard wooden plate (>30mm thickness), three times. JIS-C-0044	
■ Vibration: MIL-STD-883F: 2007.3 Frequency range 20 to 2000Hz, peak amplitude 1.52mm, peak acceleration 20g, 20min/axis X, Y & Z, total test time 4 hrs	

Technical Standards

RoHS Status	2015/863/EU - Compliant
REACH Status	(EC)1907/2006 - Compliant

Packaging Details

Packaging SPQ	Tape & Reel 1000 pcs
In tape, cut from a reel	