


**Customer Part:****Description**

- Low profile SMD crystal  
Resistance welded, hermetically sealed in an inert atmosphere, glass to metal seals on leads  
Lead wires are mounted onto a plastic former to create a gull wing mount
- Model HC49/3HSMX
- Model Issue number 17

**Frequency Parameters**

- Frequency 3.68640MHz
- Frequency Tolerance  $\pm 30.00\text{ppm}$
- Tolerance Condition @  $25^\circ\text{C} \pm 2^\circ\text{C}$
- Frequency Stability  $\pm 30.00\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Overtone Order Fundamental
- Ageing  $\pm 5\text{ppm typ per year @ } 25^\circ\text{C}$

**Outline (mm)****Electrical Parameters**

- Load Capacitance (CL) 18.00pF
- Shunt Capacitance (C0) 7pF max
- Drive Level 500 $\mu\text{W}$  max
- ESR 300.00 $\Omega$  max

**Environmental Parameters**

- Shock: 981m/s<sup>2</sup>, 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s<sup>2</sup>, 30mins in 3 mutually perpendicular planes
- Storage Temperature Range: -55 to 125°C

**Compliance**

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

**Packaging Details**

- Tape & reel in accordance with EIA-481  
Quantities below the standard reel size to be supplied on cut tape

Standard Pack Quantity: 1,000

**Sales Office Contact Details:**

UK: +44 (0)1460 270200

Email: [info@iqrdfrequencyproducts.com](mailto:info@iqrdfrequencyproducts.com)

Web: [www.iqrdfrequencyproducts.com](http://www.iqrdfrequencyproducts.com)