

Part Number: 830065253 | IQXC-90

AKA Number: LFX TAL065253




General Information




1.6 x 1.0mm SMD crystal in a hermetically sealed ceramic package.

Suitable for real time clock applications.


Dimensions [mm]



Pad Connections
1. Crystal
2. Crystal



Recommended Land Pattern [mm]



Part Number: 830065253 | IQXC-90


AKA Number: LFX TAL065253

Frequency Parameters

Frequency	32.7680 kHz
Frequency Tolerance	± 20 ppm @ 25 °C ± 5 °C
Operating Temperature	-40 °C to 85 °C
Overtone Order	Fundamental
Ageing	± 3 ppm max in 1st year @ 25 °C ± 3 °C
Frequency Stability Coefficient:	-0.036 ppm/°C ² ± 10 %

Material Parameters

Moisture Sensitivity Level (MSL) Not Applicable

Solder Reflow Graph**Note:**

- (1) The temperature used herein means the temperature on the circuit board.
- (2) Reflow is permitted 2 times.

Electrical Parameters

Load Capacitance C_L	12.5 pF
Shunt Capacitance C_0	1.2 pF typ.
Drive Level	500 nW max.
ESR	90000 Ω max.

Environmental Parameters

Storage Temperature Range: -55 °C to 125 °C

- Drop: 100 g dummy, 150 cm drop (3 directions x 10 times) onto concrete.
- Vibration: 1.5 mm amplitude, 10 Hz - 60 Hz, 15 mins in 3 mutually perpendicular planes, duration 2 hrs each plane.

Technical Standards


RoHS Status	2015/863/EU - Compliant
REACH Status	Compliant

Packaging Details

Packaging SPQ Tape & Reel 5000 pcs

- Tape & reel in accordance with EIA-481
- Quantities below the standard reel size to be supplied on cut tape.

Stability vs. Temperature



Company Address

IQD Frequency Products Ltd.
Station Road
Crewkerne
Somerset
TA18 8AR, United Kingdom