



General Information

Very low height 1.27 x 1.05 mm SMD crystal in a hermetically sealed ceramic package with a sealed metal lid.
Suitable for Real Time Clock applications.

Dimensions [mm]



Recommended Land Pattern [mm]



Part Number: 830107834801 | IQXC-146
AKA Number: LFX TAL078348

Frequency Parameters

Frequency	32.7680 kHz
Frequency Tolerance	± 20 ppm @ 25 °C ±5 °C
Overtone Order	Fundamental
Ageing	± 5 ppm max in 1st year @ 25 °C ± 3 °C
■ Turnover Temperature 25 °C ±5 °C	
■ Frequency Stability Coefficient: -0.036 ppm/°C² ±10 %	

Material Parameters

Termination Finish	Ni Au
Moisture Sensitivity Level (MSL)	Not Applicable

Manufacturing Details

- Note: the use of ultrasonic cleaning must be tested by the customer to check suitability as the device can be destroyed by this method depending upon the frequency, power, time and position in the bath.
- Reflow: 250 °C ±10 °C for 10 sec max.

Electrical Parameters

Load Capacitance CL	6 pF
Shunt Capacitance C0	1.4 pF typ.
Drive Level	0.1 µW typ. 0.3 µW max.
ESR	90000 Ω max.

Environmental Parameters

Storage Temperature Range:	-55 °C to 125 °C
■ Shock: 100 g dummy dropped 10 times in 3 axis from a height of 1500 mm onto concrete.	
■ Vibration: 1.5 mm amplitude, 10~60 Hz, 15 mins cycle time in X, Y and Z axis, 2 hrs each axis.	


Technical Standards

RoHS Status	2015/863/EU - Compliant
REACH Status	Compliant

Packaging Details

Packaging SPQ	Tape & Reel 5000 pcs
■ Tape & reel in accordance with EIA-481	
■ Quantities below the standard reel size to be supplied on cut tape.	

Stability vs. Temperature



Part Number: 830107834801 | IQXC-146

AKA Number: LFX TAL078348

Company Address

IQD Frequency Products Ltd.

Station Road

Crewkerne

Somerset

TA18 8AR, United Kingdom