

Customer Part:

Description

- Metal can package mounted on an SMD base. Resistance welded, hermetically sealed in an inert atmosphere, glass to metal seals on leads.
- Model 87SMX
- Model Issue number 11

Frequency Parameters

- Frequency 14.74560MHz
- Frequency Tolerance ±50.00ppm
- Tolerance Condition @ 25°C ±2°C
- Frequency Stability ±100.00ppm
- Operating Temperature Range -20.00 to 70.00°C
- Overtone Order Fundamental
- Ageing ±5ppm typ per year @ 25°C

Electrical Parameters

- Load Capacitance (CL) 16.00pF
- Shunt Capacitance (C0) 7pF max
- Drive Level 50µW typ, 300µW max
- ESR 30.00Ω max

Environmental Parameters

- Storage Temperature Range: -55 to 125°C
- Shock: 981m/s², 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s², 30mins in 3 mutually perpendicular planes

Manufacturing Details

- Please note that this part is NOT suitable for inverted reflow process. Please contact our application support team if this is necessary.
- Pins 2 and 3 are connected to each other and isolated from the crystal case.
- RoHS Terminations SnAgCu
- RoHS Reflow Temp 260degC 10s

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details


- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape
- Standard Pack Quantity: 1,000



Outline (mm)



Recommended Solder Pad Layout



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com