

COAXIAL CONNECTOR, BNO, X Ohm, Straight bulkhead receptacle, jack (female)

22_BNO-0-0-5/133_N

Properties

- Used with balanced twin-conductor cables with 75 ohm to 130 ohm impedance
- Suitable for applications up to 200 MHz
- Ideal for computer networks and process control



Product configuration

Interface type	Gender	Standard
BNO	jack	IEC 60169-22

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper / Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0129 kg
Mating cycles	500
Chassis torque	2 N
Flange type	round flange / others
Tab style	solder end

Environmental data

Operation temperature	-50 °C ... 125°C
-----------------------	------------------

COAXIAL CONNECTOR, BNO, X Ohm, Straight bulkhead receptacle, jack (female)
22_BNO-0-0-5/133_N

Ordering Information Table	
Item number	Item description
22541082	22_BNO-0-0-1/133_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2814 / Date of publication: 26.11.2023 / uncontrolled copy