

COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight cable plug (male)

11_716-50-23-44/033_-

Properties

- Field mountable connector series Quick-fit
- For medium and high power connection
- Applicable in frequencies up to 7.5 GHz
- IEC Standardized



Product configuration		
Interface type	Gender	Standard
7/16	plug	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	EPDM (Ethylene propylene diene rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	30 dB	1.065
2.5 GHz ... 3 GHz	28 dB	1.08

Mechanical data	
Weight	0.191 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight cable plug (male)

11_716-50-23-44/033_-

Environmental data	
Operation temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68 (24 h of water, 1 m)

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84069135	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84069135	11_716-50-23-44/033_-E	Single

Suitable cables	
Cable group	M25 - 23 mm / 50 Ohm
	M24 - 22 mm / 50 Ohm
	M23 - 22 mm / 50 Ohm
Suitable cables	SUCOFEEED_7/8_LW_LA
	SUCOFEEED_7/8_LA
	SUCOFEEED_7/8

Additional Information	
Remarks	Stripping tools: 85002265 74_Z-0-23-21 for 7/8" & 7/8"HF 84147229 74_Z-0-23-22 for 7/8" LA
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
84147229	74_Z-0-23-22	Cable stripping tool
85002265	74_Z-0-23-21	Cable stripping tool
84133924	74_Z-0-23-100	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3726 / Date of publication: 12.07.2025 / uncontrolled copy