


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-1-58/111_U

Properties

- Non-magnetic
- For cryogenic applications
- Excellent return loss
- Mechanical intermateable with PC 3.5 (3.5 mm standard) and SK (2.92 mm standard)
- Operating frequency up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Copper Beryllium Alloy	Gold Plating
Body	Copper Beryllium Alloy	Gold Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Copper Beryllium Alloy	Gold Plating
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.003 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	soldered

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)
11_SMA-50-1-58/111_U

Ordering Information Table	
Item number	Item description
85254613	11_SMA-50-1-58/111_UE
Suitable cables	
Cable group	Y18 - 1 mm / 50 Ohm
Suitable cables	MULTIFLEX_53-02
Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P57135 / Date of publication: 24.11.2025 / uncontrolled copy