

COAXIAL CONNECTOR, C, 50 Ohm, Straight cable plug (male)

11_C-50-7-15/133_N

Properties

- Easy coupling and decoupling
- Applicable in frequencies up to 11 GHz

**Product configuration**

Interface type	Gender	Standard
C	plug	IEC 60169-7_MIL-STD-348A/302

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO / Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data

Weight	0.0301 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, C, 50 Ohm, Straight cable plug (male)

11_C-50-7-15/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22541144	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22541144	11_C-50-7-15/133_NE	Single

Suitable cables	
Cable group	U43 - 7 mm / 50 Ohm
	U32 - 7 mm / 50 Ohm
Suitable cables	RG_214_/U
	GX_07272_D
Additional cables	RADOX_RF_214

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543195	76_Z-0-7-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3643 / Date of publication: 12.07.2025 / uncontrolled copy