

SENCITY® OMNI-M

1399.17.0314

Properties

- 5-Port antenna for Cellular and Wi-Fi bands
- Supports 2x2 Cellular MIMO for 3G, 4G and 5G
- Supports 3x3 Wi-Fi MIMO in all Wi-Fi 6E bands
- 2 radiators for Cellular bands and 3 radiators for Wi-Fi/WiMAX bands
- Rugged design, meets EN 60068 Standard
- Single hole mounting on cabinet or roof

**Electrical data**

	Band 1	Band 2	Band 3	Band 4
Name	Cellular 1-2	Cellular 1-2	Cellular 1-2	Cellular 1-2
Frequency	617 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.9	2	1.7	1.7
Gain	2 dBi	5 dBi	6 dBi	6 dBi
Isolation between Ports	9 dB	20 dB	20 dB	20 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	80 W	80 W	80 W	80 W

	Band 5	Band 6
Name	Wi-Fi 1-3	Wi-Fi 1-3
Frequency	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω
VSWR	2	2
Gain	6 dBi	6 dBi
Isolation between Ports	24 dB	24 dB
Ambient Temperature	25 °C	25 °C
Composite Power max	80 W	80 W

SENCITY® OMNI-M

1399.17.0314

Electrical remarks	
Remarks	Indicated VSWR and gain values are valid for installations on metallic surfaces of 500 x 500 mm. Please refer to the outline drawing to read the cable pigtail length of each port.

Ports		
	Port 1 to 2	Port 3 to 5
Port name	Cellular 1-2	Wi-Fi 1-3
Connector	N, jack (female)	N, jack (female)
Cable type	ENVIROFLEX_316_D	ENVIROFLEX_316_D
Polarization	vertical	vertical
DC grounded	Yes	Yes

Connections		
	Port 1 to 2	Port 3 to 5
Port name	Cellular 1-2	Wi-Fi 1-3
Band 1	✓	
Band 2	✓	
Band 3	✓	
Band 4	✓	
Band 5		✓
Band 6		✓

Mechanical data	
Weight	1.2 kg
Dimensions	62.5 mm x 211.5 mm (Height x Diameter)
Remarks	Corrosion: Low corrosion design according to MIL-F-14072(E), 96 hours Salt Spray test. Mounting: Shall be installed in longitudinal position to the wind/driving direction. Suitable for installation on vehicles with a maximum speed of 160 km/hr.

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7044 (light grey)
Back plate/base plate material	Aluminum

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP69
Solar radiation	UL 746C, F1

SENCITY® OMNI-M

1399.17.0314

Environmental remarks

Environmental tests: EN 60068

EN 60068-2-1 Cold temperature test Ad, -55°C, 16h

EN 60068-2-2 Dry heat test Bd +85°C, 16h

EN 60068-2-30 Damp heat cyclic test Db, +25/55°C, 2 cycles

EN 60068-2-11 Salt Mist test Ka, 96h

EN 61373 § 9 Mechanical Vibration test, Cat. 2

EN 61373 § 10 Mechanical shock test, Cat. 2

EN 60529 Ingress protection test, IP69

Additional Information

This Antenna is compliant with the Radio Equipment Directive 2014/53/EU

ETSI EN 303 413 V1.1.1 (2017-06)

Ordering information

Item description	Item number	Product name
1399.17.0314	85185301	SENCITY® OMNI-M

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35362 / Date of publication: 13.06.2025 / uncontrolled copy