

SENCITY® SC OMNI-M Antenna

1399.17.0334

Properties

- Rugged omni-directional antenna for installation on outdoor cabinets
- Supports TETRA, LTE450, 2G/3G/4G/5G cellular, Wifi 2.4/5 GHz, Wifi 6E.
- 4 separate ports for 1x TETRA/cellular and 3x3 Wifi MIMO
- Meets ETSI 300 019-1-4 class 4.1E
- Low profile housing
- Single hole mounting, easy cabling feed-through



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	TETRA/LTE450	Cellular	Cellular	Cellular
Frequency	380 MHz ... 470 MHz	694 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2.5	2	2	2
Gain	3 dBi	2 dBi	4 dBi	4 dBi
Isolation between Ports				
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7
Name	Cellular	WiFi	WiFi
Frequency	4900 MHz ... 7125 MHz	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω	50 Ω
VSWR	2	2	2
Gain	5 dBi	6 dBi	6 dBi
Isolation between Ports		20 dB	20 dB
Ambient Temperature	25 °C	25 °C	25 °C
Composite Power max	40 W	30 W	30 W

SENCITY® SC OMNI-M Antenna

1399.17.0334

Ports		
	Port 1	Port 2 to 4
Port name	Tetra 1 (yellow)	WiFi 1-3 (blue)
Connector	N, jack (female)	N, jack (female)
Cable type	ENVIROFLEX_316_D	ENVIROFLEX_316_D
Cable length	0.5 m	0.5 m
Polarization	vertical	vertical
DC grounded	Yes	Yes

Connections		
	Port 1	Port 2 to 4
Port name	Tetra 1 (yellow)	WiFi 1-3 (blue)
Band 1	✓	
Band 2	✓	
Band 3	✓	
Band 4	✓	
Band 5	✓	
Band 6		✓
Band 7		✓

Mechanical data	
Weight	1.1 kg
Dimensions	60 mm x 210 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7044 (grey)
Back plate/base plate material	Aluminium

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68, IP69k
Solar radiation	DIN 75220

Environmental remarks
Environmental tests: ETSI 300 019-4-2 class 4.1E Low corrosion designed acc. to MIL-F-14072D CE-Mark

Ordering information		
Item description	Item number	Product name
1399.17.0334	85185558	SENCITY® SC OMNI-M Antenna

SENCITY® SC OMNI-M Antenna

1399.17.0334

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35412 / Date of publication: 13.06.2025 / uncontrolled copy