

SEN CITY® Road MULTI Antenna

1399.19.0402

Properties

- Rugged vehicle rooftop multi-band antenna for commercial vehicles like bus and truck
- Supports 2G/3G/4G/5G cellular, WiFi 2.4/5 GHz, WiFi 6E
- 4 separate ports for 4x4 cellular MIMO
- Meets ISO16750 automotive standard
- Single hole mounting, easy cabling feed-through



Electrical data

	Cellular	Cellular	Cellular	Cellular
Frequency	617 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2.1	2	2
Gain	2 dBi	4 dBi	4 dBi	5 dBi
Isolation between Ports	9 dB	18 dB	15 dB	18 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	WiFi	WiFi
Frequency	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω
VSWR	2	2
Gain	6 dBi	6 dBi
Isolation between Ports	24 dB	24 dB
Ambient Temperature	25 °C	25 °C
Composite Power max	30 W	30 W

SENCITY® Road MULTI Antenna

1399.19.0402

Electrical remarks

Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1x1 m or larger.
---------	--

Ports

	Cell 1-2 (white)	WiFi 1-2 (blue)
Connector	SMA, plug (male)	SMA, plug (male)
Cable type	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM
Cable length	0.3 m	0.3 m
Polarization	vertical	vertical
DC grounded	Yes	Yes

Connections

	Cell 1-2 (white)	WiFi 1-2 (blue)
Band 1	✓	
Band 2	✓	
Band 3	✓	
Band 4	✓	
Band 5		✓
Band 6		✓

Mechanical data

Weight	1.1 kg
Dimensions	60 mm x 210 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data

Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminium

Environmental data

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68, IP69k
Flammability rating	ECE-R118
Solar radiation	DIN 75220
Standards	Automotive ISO 16750

Environmental remarks

Environmental tests: ISO 16750:2012/2010
 Low corrosion designed acc. to MIL-F-14072D
 E-Mark
 CE-Mark

SENCITY® Road MULTI Antenna

1399.19.0402

Ordering information

Item description	Item number	Product name
1399.19.0402	85192449	SENCITY® Road MULTI Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P35213 / Date of publication: 04.06.2025 / uncontrolled copy