

SENCITY® Urban 100 Omni MIMO 2x2 antenna

1399.32.0004

Properties

- Outdoor MIMO 2x2 omnidirectional antenna for 4G and 5G frequency bands
- 2500-2690, 3300-3800, 3800-4200MHz
- Very low PIM
- With NEX10 connectors
- Compact solution with very high isolation between ports to maximize MIMO performances



Electrical data			
	Band 1	Band 2	Band 3
Frequency	2500 MHz ... 2690 MHz	3300 MHz ... 3800 MHz	3800 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω
VSWR	2	2	2
Gain	2 dBi	2.5 dBi	2.5 dBi
HPBW vertical	65 °	55 °	55 °
Isolation between Ports	30 dB	30 dB	30 dB
Ambient Temperature	70 °C	70 °C	70 °C
Composite Power max	100 W	70 W	60 W

Electrical remarks	
IMD level	-150 dBc at carrier power 2x 43 dBm

Ports		
	Port 1	Port 2
Connector	NEX10, jack (female)	NEX10, jack (female)
Polarization	vertical	horizontal

Connections		
	Port 1	Port 2
Band 1	✓	✓
Band 2	✓	✓

SENCITY® Urban 100 Omni MIMO 2x2 antenna

1399.32.0004

Connections		
Band 3		
Mechanical data		
Weight	0.42 kg	
Dimensions	96 mm x 117 mm (Height x Diameter)	
Material data		
Radome material	PC (Polycarbonate)	
Radome colour	RAL 7035 (light-grey)	
Environmental data		
Operation temperature	-45 °C ... 70 °C	
Environment (application)	Indoor/Outdoor	
Ingress protection (IP Rating)	IP66	
Environmental remarks		
EN 300 019-2-4 4.1E: Salt mist IEC60068-2-11 Ka:35°C/5%NaCl/10d Damp heat (steady state) IEC60068-2-78 Cab 93% +30°C 10d, (cycle) IEC60068-2-30 Db 93%-100% +10°C 2cycles Vibration: IEC60068-2-6 Fc (sinusoidal), IEC60068-2-64 Fh (random) Shocks IEC60068-2-27 Ea Type II and Type L Wind load IEC 60721-3-3 with max wind speed 180Km/h		
Antenna accessories		
Item description	Item number	Product name
9091.99.0274	85113372	SENCITY® Antenna down- and sidetilt Bracket
9091.99.0238	84084452	SPOT-S Antenna Down- and Sidetilt Bracket
Ordering information		
Item description	Item number	Product name
1399.32.0004	85113723	SENCITY® Urban 100 Omni MIMO 2x2 antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
 DOCUMENT PIM-P3230 / Date of publication: 19.08.2025 / uncontrolled copy