

SENCITY® Rail MIMO Low Profile Antenna with GPS

1399.99.0072

Properties

- Railway rooftop antenna for 2G/3G/4G/5G cellular and Wi-Fi 6E bands
- Supports 2x2 Cellular MIMO for 3G, 4G and 5G
- Supports 2x2 Wi-Fi MIMO in all Wi-Fi 6E bands
- Rugged design, meets EN 50155 Railway Standard and Fire retardant according to EN 45545-2 and NFPA-130
- Includes embedded passive GPS antenna (requires separate LNA such as 86010142)
- High Voltage and High Current protection for use under catenary lines
- Extremely low profile (40mm)



Electrical data

	Band 1	Band 2	Band 3	Band 4
Name				
Frequency	694 MHz ... 960 MHz	1350 MHz ... 1450 MHz	1450 MHz ... 2700 MHz	3300 MHz ... 4900 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.8	1.9	1.6	1.8
Gain	5 dBi	7 dBi	6.5 dBi	7.5 dBi
Isolation between Ports	15 dB	16 dB	20 dB	25 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7
Name			GPS
Frequency	4900 MHz ... 5150 MHz	5150 MHz ... 7125 MHz	1574.4 MHz ... 1576.4 MHz
Impedance	50 Ω	50 Ω	50 Ω
VSWR	1.8	1.8	1.8
Gain	9 dBi	8 dBi	

SENCITY® Rail MIMO Low Profile Antenna with GPS

1399.99.0072

	Band 5	Band 6	Band 7
Isolation between Ports	25 dB	25 dB	
Ambient Temperature	25 °C	25 °C	
Composite Power max	40 W	40 W	

Electrical remarks

Remarks	Indicated VSWR and gain values are valid for a metallic ground plane of 0.5 x 1 m or larger.
---------	--

Ports

	Port 1	Port 2	Port 3
Port name	Cell/W-Fi 1	Cell/Wi-Fi 2	GPS
Connector	N, jack (female)	N, jack (female)	TNC, plug (male)
Cable type	RADOX_RF_316_D	RADOX_RF_316_D	RADOX_RF_316_D
Cable length	0.24 m	0.18 m	0.16 m
Polarization	vertical	vertical	circular right
DC grounded	Yes	Yes	Yes

Connections

	Port 1	Port 2	Port 3
Port name	Cell/W-Fi 1	Cell/Wi-Fi 2	GPS
Band 1	✓	✓	
Band 2	✓	✓	
Band 3	✓	✓	
Band 4	✓	✓	
Band 5	✓	✓	
Band 6	✓	✓	
Band 7			✓

Mechanical data

Weight	1.3 kg
Dimensions	40 mm x 108 mm x 474 mm (Height x Width x Depth)
Remarks	High-voltage-protection: no voltage on RF port, if catenary line touches antenna (EN 50124-1, 3.8 kVDC, 25 kVAC) High-current-protection: Designed acc. to UIC 533, DC-grounded antenna element (protection against lightning and short circuit with catenary lines(40kA/0.125s). Corrosion: Low corrosion design acc. to MIL-F-14072(E). Mounting: Shall be installed in longitudinal position to the wind/driving direction. 4x composite sealing washers included for silicone-free sealing of the mounting screws.

Material data

Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminum
Back plate/base plate plating	Passivated (Plating)
Back plate/base plate colour	Grey

SENCITY® Rail MIMO Low Profile Antenna with GPS

1399.99.0072

Environmental data	
Operation temperature	-55 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP69
Flammability rating	EN 45545-2 R24 HL3
Solar radiation	UL 746C, F1

Environmental remarks

Flammability rating: EN45545-2:2013 + A1:2015, NFPA-130:2017
 Tested according to ISO 4589-2:2017, NFX 70-100-1:2006, ISO 5659-2:2011.

Environmental tests: EN 50155:2018-05
 §13.4.6 EN 60068-2-1:2008-01 Cold temperature test Ab, -55°C, 16h
 §13.4.5 EN 60068-2-2:2008-01 Dry heat test Be +85°C, 16h
 §13.4.7 EN 60068-2-30:2006-06 Damp heat cyclic test Db, +25/55°C, 2 cycles
 §13.4.10 EN 60068-2-11:2000-02 Salt mist test, 96h
 §13.4.11 EN 61373:2011-04 § 8, Cat. 1B Broadband Random Vibration
 §13.4.11 EN 61373:2011-04 § 9, Cat. 1B Increased Random Vibration
 §13.4.11 EN 61373:2011-04 § 10, Cat. 1B Mechanical shock
 §13.4.12 Ingress Protection EN 60529:2014-09 IP6X, IPX5, IPX6, IPX8, IPX9

Related Products

9091.99.0235 Sencity Rail antenna grounding kit
 9091.99.0257 Sencity Rail - M10 sealing washer kit

Additional Information

This product meets the Deutsche Bahn specifications for rolling stock equipment.
 Protected by Patents: DE202015009331(U1), US10116056(B2), CN106663861B.

Ordering information

Item description	Item number	Product name
1399.99.0072	85106685	SENCITY® Rail MIMO Low Profile Antenna with GPS

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
 DOCUMENT PIM-P35339 / Date of publication: 20.08.2025 / uncontrolled copy