

SENCITY® Spot-S Indoor Antenna

1319.19.0005

Properties

- SENCITY Spot-S planar indoor DECT antenna
- Gain of 8 dBi with Circular Right Hand polarisation
- Working range: 1850 to 1990 MHz
- Half power beamwidth of 70° (vertical) and 70° (Horizontal)
- Wall mounting socket included

**Electrical data**

	Band 1
Frequency	1850 MHz ... 1990 MHz
Impedance	50 Ω
VSWR	1.5
Gain	8 dBi
HPBW vertical	70 °
HPBW horizontal	70 °
Front to back ratio	20 dB
Vertical Electrical Tilt	0 °
Ambient Temperature	25 °C
Composite Power max	10 W

Ports

	Port 1
Connector	SMA, jack (female)
Polarization	circular right
DC grounded	No

Mechanical data

Weight	0.115 kg
Dimensions	101 mm x 95 mm x 32 mm (Height x Width x Depth)
Windload	front: 15 N at 160 km/h
Remarks	Mounting socket material: ASA and aluminum Mounting socket color: RAL 7042 (dark grey)

SENCITY® Spot-S Indoor Antenna

1319.19.0005

Material data	
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7035 (light-grey)
Back plate/base plate material	ASA (acrylic ester-styrene-acrylonitrile)
Back plate/base plate colour	RAL 7042 (dark-grey)

Environmental data	
Operation temperature	-40 °C ... 80 °C
Storage temperature	-40 °C ... 80 °C
Transport temperature	-40 °C ... 80 °C
Environment (application)	Indoor

Antenna accessories		
Item description	Item number	Product name
9091.99.0080	22652651	Planar Indoor Antenna Sidetilt Bracket

Ordering information		
Item description	Item number	Product name
1319.19.0005	22650451	SENCITY® Spot-S Indoor Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31266 / Date of publication: 30.07.2025 / uncontrolled copy