

SENCITY® Spot-S Indoor Antenna

1319.26.0027

Properties

- Compact Indoor antenna for DECT bands between 1880 and 1930 MHz
- Gain of 8 dBi with dual slant +/-45° polarisation
- Half power beamwidth of 75° (vertical) and 85° (Horizontal)
- Wall mounting socket included
- Integrated TNC female interface

**Electrical data**

	Band 1
Frequency	1880 MHz ... 1930 MHz
Impedance	50 Ω
VSWR	1.5
Gain	8 dBi
HPBW vertical	75 °
HPBW horizontal	85 °
Isolation between Ports	30 dB
Front to back ratio	12 dB
Vertical Electrical Tilt	0 °
Ambient Temperature	25 °C
Composite Power max	10 W

Ports

	Port 1	Port 2
Connector	TNC, jack (female)	TNC, jack (female)
Polarization	-45° slant	+45° slant
DC grounded	No	No

Connections

	Port 1	Port 2
Band 1	✓	✓

SENCITY® Spot-S Indoor Antenna

1319.26.0027

Mechanical data	
Weight	0.11 kg
Dimensions	101 mm x 95 mm x 32 mm (Height x Width x Depth)
Windload	front: 15 N at 160 km/h
Remarks	Mounting socket material: ASA and aluminum Mounting socket color: RAL 7042 (dark grey)

Material data	
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7035 (light-grey)
Back plate/base plate material	Aluminum
Back plate/base plate colour	RAL 7042 (dark-grey)

Environmental data	
Operation temperature	-40 °C ... 80 °C
Storage temperature	-40 °C ... 80 °C
Transport temperature	-40 °C ... 80 °C
Environment (application)	Indoor

Ordering information	
Item number	Item description
22659404	1319.26.0027

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31267 / Date of publication: 07.02.2025 / uncontrolled copy