

SENCITY® Omni-S Dome

1399.17.0040

Properties

- Compact omnidirectional antenna for Wi-Fi and Cellular bands between 2400 MHz and 6000 MHz
- Dual-band IEEE 802.11 a/b/g/h
- WLAN, LTE 2.6, WiMAX
- For indoor application



Electrical bands			
	Band 1	Band 2	Band 3
Frequency	2400 MHz ... 2500 MHz	2500 MHz ... 4900 MHz	4900 MHz ... 6000 MHz
VSWR	1.6	1.5	1.5
Impedance	50 Ω	50 Ω	50 Ω
Gain	4 dBi	4 dBi	7.5 dBi
HPBW horizontal	360 °	360 °	360 °
Ambient Temperature	25 °C	25 °C	25 °C
Composite Power max	160 W	120 W	120 W

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	No

Mechanical data

Weight	0.3 kg
Dimensions	43 mm x 86 mm (Height x Diameter)
Windload	front: 10 N at 160km/h, Wind Speed survival: 160 km/h


Interface and material data

Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7035 (light-grey)
Back plate/base plate material	Aluminum

SENCITY® Omni-S Dome
1399.17.0040

Environmental data	
Operation temperature	-40 °C ... 80 °C
Storage temperature	-40 °C ... 80 °C
Transport temperature	-40 °C ... 80 °C
Environment (application)	Indoor

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3274 / Date of publication: 19.06.2024 / uncontrolled copy